

Wall Mount Cabinets

Pivoting Wall Mount Cabinets



Colour is black RAL 7021. IP 20, IK 08

OR-43500618

Part No.	Units	Description
OR-43500618	9 U	600 mm W x 600 mm D x 500 mm H
OR-43500089	12 U	600 mm W x 600 mm D x 600 mm H
OR-43500131	16 U	600 mm W x 600 mm D x 800 mm H
OR-43500090	21 U	600 mm W x 600 mm D x 1000 mm H

Fixed Wall Mount Cabinets 400 mm deep



Colour is black RAL 7021. IP 20, IK 08

OR-43500128

Part No.	Units	Description
OR-43500128	6 U	600 mm W x 400 mm D x 350 mm H
OR-43500129	9 U	600 mm W x 400 mm D x 500 mm H
OR-43500130	12 U	600 mm W x 400 mm D x 600 mm H

Fixed Wall Mount Cabinets 580 mm deep



Colour is black RAL 7021. IP 20, IK 08

OR-43500109

Part No.	Units	Description
OR-43500109	9 U	600 mm W x 580 mm D x 500 mm H
OR-43500110	12 U	600 mm W x 580 mm D x 600 mm H
OR-43500111	16 U	600 mm W x 580 mm D x 800 mm H

General features

- > Metal Wall Mount Cabinets. The cabinets have a curved safety glass front door, removable side panels and a solid rear door, all with locks 2433A
- > RAL 7021 textured polyester coating with excellent resistance to corrosion and scratch
- > Index of protection (weatherproofing) against ingress of solid bodies and liquids: IP 20
- > Index of protection against mechanical impacts: IK 08
- > Permissible load rating: 3 kg/U (i.e. 48 kg for 16 U cabinet)

Conformity to standards

Cabinets comply with the following standards:

IEC 60529 EN 60529	(NF C 20-010) Degrees of protection provided by enclosures (IP code)
IEC 62262 EN 62262	(EN 50102, NF C 20-015) Degrees of protection provided by enclosures for electrical equipment against external mechanical impact (IK code).
IEC 60950-1 EN 60950-1 C 77-210-1	Information technology equipment - Safety
EIA-310-D	Cabinets, racks, panels and associated equipment (ANSI/EIA/310-D-1992).
IEC 60297-1 & 2 DIN 41414-7	(NF C 20-150, NF C 20-151) Dimensions of mechanical structures of the 482.6 mm (19 in) series.

Cabinets are designed to be integrated into installations that comply with the following standards:

EN 50173-1	Information technology - Generic cabling systems.
EN 50174-1 & 2 C 90-480-1 & 2	Information technology - Cabling installation.
ISO IEC 11801	Information technology - Generic cabling for customer premises.
NF C 15-100 Partie 4-41	Low voltage electrical installations - Rules.
UTE C90-483	Residential cabling of communication networks

Hinged Wall Mount Brackets



OR-604004068

Ortronics hinged wall mount brackets meet smaller system requirements and allow easy access to the rear of the panels. Holes in back allow for rear cable feed through. These brackets are available in four heights, with 19" #12-24 threaded EIA pattern. Fully assembled. Colour is black.

Part No.	Units	Description
OR-604004396	2 U	482.6 mm W x 152.4 mm D x 88.9 mm H
OR-604004301	3 U	482.6 mm W x 152.4 mm D x 133.35 mm H
OR-604004068	4 U	482.6 mm W x 152.4 mm D x 177.8 mm H
OR-604004645	6 U	482.6 mm W x 152.4 mm D x 266.7 mm H