

## Hospital Grade Duplex GFCI, Red

1595HGRED



From the innovator of the product category, comes a full range of Pass & Seymour®GFCI receptacles to enhance safety, shorten installation times and increase productivity on the jobsite. Our hospital-grade GFCI meet rigorous requirements of Hospital Grade supplement of UL498.

### features & benefits

- **Patented SafeLock™ Protection for More Safety** - shuts off power to the receptacle if there's a ground fault, if the GFCI is miswired, and even if the GFCI fails. This prevents the unsafe condition of power without protection.
- **Tamper-Resistant: Automatic shutter system** prevents young children from inserting common objects such as hairpins or keys.
- **The most durable GFCI available** - exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- **Audible Alarm notifies end user of tripped GFCI.** Provides Supplemental notification (along w/Trip Indicator Light - red LED). Alarm can be turned on/off.
- **Side or internal screw-pressure-plate back wire termination** speeds installation; takes #14 – #10 AWG stranded or solid, copper or copperclad conductors.
- **Two back-wire holes per termination** add wiring flexibility, eliminate pigtail, and save box space.
- **Ground terminal back-wire clamp** for fast installation.
- **High-impact-resistant thermoplastic construction** for superior strength and durability.
- 10kA short circuit rating.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### specifications

#### General Info

Color: Red  
Available Colors: White, ivory, light almond, red, brown, black, gray  
Type: Duplex  
Special Features: Tamper Resistant  
Style: Decorator

#### **Listing Agencies/Third Party Information**

RoHS: No  
CSA Standard: C22.2 No. 42, 144  
CUL Listing No: E42190  
cULus: Yes  
cUL Standard: Yes  
Federal Spec: Yes  
Fed Spec Number: WC596  
UL Listing No: UL498  
UL Listed: Yes  
UL Standard: Yes  
UN SPS C: 39121614

#### **Dimensions**

Depth U S: 0.98"  
Height U S: 4.2"  
Length U S: 4.20"  
Width U S: 1.72"

#### **Technical Information**

Amps: 15A  
NEMA Configuration Number: 5-15R  
NEMA Rating: WD-1, WD-6  
Volts: 125V  
Volts A C: 125  
Grade Type: Hospital

#### **Buy American Act Compliance**

Country of Origin: CHINA  
Buy American Act Status: No