

Combination Tamper- Resistant 20A Nightlight/GFCI, White

2095NTLTRW



Our nightlight/GFCI include a GFCI outlet, plus an LED nightlight with automatic ON/OFF that remains cool to the touch and is remarkably energy efficient and durable—the life expectancy is more than 20 years. Ideal for safe nighttime navigation in bathrooms, hallways, kitchens, nurseries, on stairs and more.

features & benefits

- Protects children: patented shutter system helps prevent improper insertion of foreign objects.
- Meets National Electrical Code® Tamper-Resistant requirements.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Sealed nightlight with high impact-resistant Lexan® lens prevents tampering.
- Nightlight uses cooler LED illumination.
- Energy-efficient LED has average 20-year life expectancy, eliminating bulb replacement.
- LED Rated at 186 milliwatts 120V.
- Two receptacles.
- Photocell turns nightlight ON in dark, OFF in daylight.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10-#14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- 10kA short circuit wiring.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long strap.
- Button colors match the device face.

- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- For covering patents, see www.legrand.us/patents.

specifications

General Info

Color: White
Available Colors: White, ivory, light almond, red, gray
Type: Nightlight/GFCI
Special Features: Tamper Resistant
Style: Decorator

Listing Agencies/Third Party Information

RoHS: No
CSA Standard: C22.2 No. 42, 144
CUL Listing No: E42190
cULus: Yes
cUL Standard: Yes
Federal Spec: Yes
Fed Spec Number: WC596
UL Listing No: UL498
UL Listed: Yes
UL Standard: Yes
UN SPS C: 39121614

Dimensions

Depth U S: 1.13"
Height U S: 4.2"
Length U S: 4.20"
Width U S: 1.72"

Technical Information

Amps: 20A
NEMA Configuration Number: 5-20R
NEMA Rating: WD-1, WD-6
Volts: 125V
Volts A C: 125

Buy American Act Compliance

Country of Origin: CHINA
Buy American Act Status: No