

TradeMaster Decorator Receptacle

TM885W



Decorator duplex receptacle with pressure plate. 15 amp, 125 volt, White.



features & benefits

- Longer steel straps than competitive devices, still fits under a standard wall plate.
- High-impact thermoplastic face and back body eliminate cracks, breaks, and callbacks.
- Ultrasonic welding of face to back body.
- Patented design provides better plug retention.
- External screw-pressure-plate back wire on all four terminal screws and ground screw eliminates wrapping.
- Accepts #12 and #14 stranded and solid wire.
- Break-off tabs that are big enough to grab hold of -- even if contact screws are backed out.
- Scored deeper for fast, clean breaks every time.
- All four contact screws and the ground screw are backed out.
- All screws are tri-drive.

specifications

General Info

Color: White
Number Of Poles: 2
Number Of Wires: 3

Listing Agencies/Third Party Information

cULus: Yes
Federal Spec: No

UL Listing No: UL498
UL Standard: Yes
UN SPS C: 39121704

Dimensions

Depth U S: 1"
Height U S: 3.31"
Width U S: 1.29"

Technical Information

Amps: 15
Volts: 125

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant