



Residential & Light Commercial Dimmers & Fan Speed Controls Wide Slide Series


Pass & Seymour




Full-On Bypass

When the dimmer is placed in the full-On position, the dimming circuitry is bypassed by latching contacts. This feature allows for 100% lighting output and extends dimmer life by eliminating heat build-up.

Features	
<ul style="list-style-type: none"> Maximum ratings are for continuous full load. Many 1000W models fit standard Decorator plates. RFI suppression built in. Full-On bypass. 	<ul style="list-style-type: none"> Preset "ON/OFF" switch automatically returns controlled lights to preset level without readjusting dimmer setting. 600W maximum rated dimmers can be ganged without de-rating.



P 90680 P 90683
N 90681



P 91180 P 91183
N 91181

P = Preset
N = Non-Preset

Catalog Number		Description	Ratings	Color
Single Pole	Three-Way			
600W Incandescent Specification Grade Slide Dimmers				
90680I* 90680W* 90680GRY 90680LA*	90683I* 90683W* 90683GRY 90683LA*	Preset	120V 600W max.	Ivory White Gray Light Almond
90681I* 90681W* 90681GRY 90681LA*		Non-Preset	120V 600W max.	Ivory White Gray Light Almond
1000W Incandescent Specification Grade Slide Dimmers				
91180I 91180W 91180GRY 91180LA	91183I 91183W 91183GRY 91183LA	Preset	120V 1000W max.	Ivory White Gray Light Almond
91181I 91181W 91181LA		Non-Preset	120V 1000W max.	Ivory White Light Almond

* Available in VisionPak™ packaging, add "V" to Catalog Number. Example: 90680IV.

Max. Load Rating	Fins Removed	
	One Side	Two Side
De-Rating Chart		
1000W	800W	700W

Note: Each side removed reduces plate size by 3/8".

Slide Dimmer 3-Way Wiring Diagram

