Pass & Seymour

la legrand

Wall Plates Blank Plates – Box Mounted

Standard Size Plastic & Metal

		Ι	Τ	Metal		
		Nylon	Thermoset	Me	tal	
Description	Color	TradeMaster® Plates	Smooth	Material	Smooth	
Blank Plates – Box Mounted						
One Gang Blank – Box Mtd.	Ivory White Brown Gray Black Red Light Almond	TP13I TP13W TP13 TP13GRY TP13BK TP13RED TP13LA	SP13I SP13W SP13 SP13GRY SP13LA	Aluminum Brass Polished Brass 430S/S 302S/S 302S/S 11/2" Screws) Brushed Bronze Chrome	SA13 SB13 SB13PB SL13 SS13 SS13.5 SB13BZ SB13CH	
Two Gang Blank – Box Mtd.	Ivory White Brown Gray Black Light Almond	TP23I TP23W TP23 TP23GRY TP23BK TP23LA	SP23I SP23W SP23 SP23GRY SP23LA	Aluminum Brass Polished Brass 430S/S 302S/S 302S/S (1/2" Screws) Brushed Bronze Chrome	SA23 SB23 SB23PB SL23 SS23 SS23 SS23.5 SB23BZ SB23CH	
Three Gang Blank – Box Mtd.	Ivory White Brown Gray Light Almond		SP33I SP33W SP33 SP33GRY SP33LA	Polished Brass 302S/S 302S/S (1/2" Screws)	SB33PB SS33 SS33.5	
Four Gang Blank – Box Mtd.	Ivory White Brown Gray		SP43I SP43W SP43 SP43GRY	302S/S	SS43	
Five Gang Blank – Box Mtd.				302S/S	SS53	
Six Gang Blank – Box Mtd.				302S/S	SS63	
Seven Gang Blank – Box Mtd.				302S/S	SS6013	
Eight Gang Blank – Box Mtd.				302S/S	SS6023	

Pass & Seymour

□ legrand

Wall Plates Specifications



SP Series



Thermoset



Nylon TP Series



Screwless Polycarbonate SWP & SW Series

Application

Pass & Seymour/Legrand's broad line of Standard Size Plastic and Metal Wall Plates features the most complete range of types, sizes, colors, and finishes available. Choose from more than 1,900 standard plates in non-combustible thermoset plastic material, self-extinguishing nylon material, screwless polycarbonate material, or attractively finished metal, for residential, commercial, institutional, and industrial applications. All plastic wall plates color match to Pass & Seymour/Legrand devices.

Thermoset Plastic Wall Plates Features

- Molded of non-combustible mar-proof material.
- Available in "SP" series in Standard, Junior-Jumbo, and Jumbo sizes
- Seven standard colors available Ivory, White, Brown, Gray, Black, Red, and Light Almond.
- Individually wrapped with color-matching screws
- Resistant to discoloration, grease, oil, solvent and moisture.
- Nominal thickness, .070"

TradeMaster® Thermoplastic Wall Plates Features

- Molded of rugged, practically indestructible self-extinguishing nylon. ("TP" series only.)
- Available in "TP" series, extra 3/16" width and height than Standard size plates; and "TPJ" series, extra 3/16" width and height than Junior-Jumbo size plates.
- Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.
- Preferred for hospital, industrial, institutional, and other high-abuse applications.
- Nominal thickness, .070"

Screwless Polycarbonate Wall Plates Features

- Molded of .065" thick polycarbonate with matte finish.
- 2-piece plastic subplate made of polycarbonate ("SWP" Series only).
- Metal subplate made of .042" zinc-plated steel ("SW" Series only).
- Extra 1/8" width and height than Standard size plates.
- Available in Ivory, White, Brown, Gray, Black, and Light Almond.
- Oversized opening to accommodate all NEMA 26 decorator-style openings.

Metal Wall Plates Features

- Constructed of corrosion-resistant stainless steel, brass, aluminum, chrome, brushed bronze or galvanized steel.
- Standard, Jumbo, and Tandem size plates available, as well as special Panel size plates up to 5-gangs high and 10-gangs wide.
- Packaged in protective film, with finish-matching
- Variety of special plated finishes. Paintable to match plastic plates.
- Can be silk-screened or engraved, and custom punched with over 300 opening styles.

Materials

- Type 302 Stainless Steel, non-magnetic, .032" nominal thickness, brushed finish. This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion. Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive
- Type 430 Stainless Steel, magnetic, .032" nominal thickness, brushed finish. Less corrosionresistant than Type 302, but ideal for general service in high abuse applications in industrial plants, commercial, and institutional buildings.
- Chrome, Brushed and Polished Brass, .040" thick. 70% copper, 30% zinc alloy gives warm, appealing finish to modern decor as well as retrofit applications. Lacquered to prevent corrosion.
- Aluminum, .040" thick. Lustrous satin finish. Lacquered to prevent corrosion.
- Galvanized Steel. Used only for Handy Box
- Brushed Bronze, .040" thick. 90% copper, 10% zinc. Lacquered to prevent corrosion.



302 Stainless Steel



Polished Brass



Brushed Brass




Aluminum

Wall Plates Specifications


Pass & Seymour

la legrand

Standard Size Wall Plates						
■ Standard size wall plates for all applications. ■ Available in plastic and metal only. ■ Best fit for surface mount boxes.						
Dimensions						
1 gang	2.75" x 4.5"	4 gang	8.125" x 4.5"	7 gang	13.62" x 4.5"	
2 gang	4.56" x 4.5"	5 gang	10" x 4.5"	8 gang	15.44" x 4.5"	
3 gang	6.375" x 4.5"	6 gang	11.812" x 4.5"			



STANDARD



TRADEMASTER STANDARD

TradeMaster® Wall Plates ■ Extra 3/16" width and height than Standard size wall plates. ■ Provide better sheet rock coverage with standard size appearance. ■ Available in unbreakable nylon 6 construction only. ■ Screws pre-installed in the duplex, toggle, and decorator single gang plates. **Dimensions** 1 gang 2.9375" x 4.6875" 3 gang 6.563" x 4.6875" 5 gang 10.188" x 4.6875" 4.75" x 4.6875" 8.375" x 4.6875" 6 gang 12" x 4.6875" 2 gang 4 gang


Screwless Polycarbonate Wall Plates

- Extra 1/8" width and height than Standard size wall plates.
- Provide better sheet rock coverage with standard size appearance.
- Molded of .065" thick polycarbonate.
- 2-piece plastic subplate made of polycarbonate ("SWP" Series only).
- Metal subplate made of .042" zinc-plated steel ("SW" Series only).
- Available in 5 metallic and 3 wood finishes.

■ Oversized opening to accommodate all NEMA 26 decorator-style openings.						
Wall Plate Dimensions						
1 gang	3.10" x 4.87"	3 gang	6.724" x 4.87"	5 gang	10.348" x 4.87"	
2 gang	4.912" x 4.87"	4 gang	8.536" x 4.87"	6 gang	12.16" x 4.87"	
Subplate Dimensions						
1 gang	2.85" x 4.62"	3 gang	6.474" x 4.62"	5 gang	10.098" x 4.62"	
2 gang	4.662" x 4.62"	4 gang	8.286" x 4.62"	6 gang	11.910" x 4.62"	

-3.10"


SCREWLESS



JUNIOR-JUMBO



TRADEMASTER JUMBO



Junior-Jumbo Wall Plates

- Extra 3/8" width and height than Standard size wall plates. ■ Available in plastic and metal only.
- Additional coverage for sheet rock gaps.

Dimensio	ns		
1 gang	3.125" x 4.87"	3 gang	6.75" x 4.87"
2 gang	4.93" x 4.87"	4 gang	8.56" x 4.87"

TradeMaster Jumbo Wall Plates

- Extra 3/16" width and height than Junior-Jumbo size wall plates.
- Provide additional coverage for sheet rock gaps, matching the appearance of the TradeMaster Plates.
- Available in unbreakable nylon 6 construction only.
- Screws pre-installed in the duplex, toggle, and decorator single gang plates.

Dimensions

3 gang 6.9375" x 5.0625" 1 gang 3.3125" x 5.0625" 2 gang 5.125" x 5.0625" 4 gang 8.75" x 5.0625"

Jumbo Wall Plates

- Extra 3/4" width and height than Standard size wall plates. ■ Largest size wall plates to cover larger wall damage.
- - Available in plastic and metal only.

Dimensions

1 gang	3.5" x 5.25"	3 gang	7.12" x 5.25"	
2 gang	5.31" x 5.25"	4 gang	8.93" x 5.25"	