Pass & Seymour

□ legrand

2.620" 4.19"

TM870STMLACC

Switches

Decorator & Specification Grade Combination Momentary & Maintained Contact Switches

15A, 120 & 120/277VAC

Features

- Designer-style satin-finish rocker.
- High-impact resistant thermoplastic construction.
- External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.
- Push wire #14 AWG.
- Narrow back body leaves more room for wires in the box.
- Extra-long, through-body strap eliminates floating installations and imperfect applications.
- Smooth, quiet paddle action.
- Easy-access green hex head ground screw.
- Tri-drive ground, terminal and mounting screws.

				3rd Party Compliance				
Catalog Number	Rati A.	ng VAC	Color	(h)	€.			
Oatalog Hamber	Λ.	VA0	00101	UL20	C22.2 111			
Single Pole Decorator Momentary Contact Switches								
TM870STMICC	15	120/277	Ivory	•	•			
TM870STMWCC	15	120/277	White	•	•			
TM870STMLACC	15	120/277	Light Almond	•	•			
TM870STMBKCC	15	120/277	Black	•	•			

ENUSIVE PROPERTY



Momentary Contact



Maintained Contact

Features

- Unique "Up/Down" switches match the look and feel of standard decorator switches.
- Impact-resistant face and body.
- Side and external screw-pressure-plate back wire accepts #12 and #14 AWG.
- All screws are tri-drive.

- Full wraparound heavy-gauge steel strap is plated for corrosion resistance and features lock-in tabs.
- Patent-pending split circuit tab easily accessible, and can be reinstalled without a tool.

			3rd Party Compliance					
Catala v Navada v	Rating	0-1	c (UL) us (UL)	(h)				
Catalog Number	A. VAC	Color	cULus UL20	UL508				
Specification Grade Double Throw Momentary Contact Switches								
TM811DTMO	15 120	lvory	•	•				
TM811DTMOW	15 120	White	•	•				
TM811DTMOLA	15 120	Light Almond	•	•				
Specification Grade Double Throw Maintained Contact Switches								
TM811DTMA	15 120	lvory						
TM811DTMAW	15 120	White	• •					
TM811DTMALA	15 120	Light Almond	• •					