

GFCI AND ISOLATED GROUND PROTECTION — ALL IN ONE DEVICE.



2095IGTRO

The industry's first
Isolated Ground GFCI.

As computers, cash registers and other electronics become more common in areas like commercial kitchens and laboratories, it's important to protect workers who use them from the possibility of electric shock.

We've made that easy with the new Pass & Seymour Isolated Ground GFCI by Legrand.

It's the first-ever GFCI designed specifically for receptacles installed on isolated ground circuits, and it's a great way to provide shock protection for those using sensitive electronic equipment near water or other liquids.

The Pass & Seymour Isolated Ground GFCI — it's just another way we're helping customers solve their complex commercial electrical challenges, while meeting the ever-expanding *National Electric Code*® (*NEC*®) requirements for GFCI protection. All models are Tamper-Resistant. Also available in Hospital Grade.

Side or internal screw-pressure plate back-wire termination speeds installation; takes #14-#10 AWG stranded or solid, copper or copperclad conductors.

Two back-wire holes per termination add wiring flexibility, eliminate pigtail, and save box space.

Patented SafeLock™ Protection for More Safety — shuts off power to the receptacle if there's a ground fault, if the GFCI is miswired, and even if the GFCI fails. This prevents the unsafe condition of power without protection.

Pre-stripped stranded wire lead for isolated ground termination.



Automatic shutter system prevents young children from inserting common objects such as hairpins or keys.

Trip indicator light makes it easy to identify a tripped condition.

The most durable GFCI available — exceeds UL943 voltage surge requirements; survives 100X the required UL 3kA/6kV voltage surge test cycles.

GFCI Receptacle's grounding system is isolated from the building's grounding system.

2095IGTRO

PART NO.	DESCRIPTION	RATINGS		COLORS	NEMA Config.	*COLOR DESIGNATION
		A.	V.			
1595IGTR*	TradeMaster® Isolated Ground Tamper-Resistant Duplex GFCI	15	125	W, I, BK, LA, O, -	5-15R	W White I Ivory - Brown GRY Gray BK Black LA Light Almond RED Red O Orange
2095IGTR*	Specification Grade Isolated Ground Tamper-Resistant Duplex GFCI	20	125	W, I, BK, LA, GRY, RED, O, -	5-20R	
1595IGHGTR*	Hospital Grade Isolated Ground Tamper-Resistant Duplex GFCI	15	125	W, I, LA, GRY, RED, O, -	5-15R	
2095IGHGTR*		20	125		5-20R	

All GFCIs are Fed Spec, FSUL Listed. US LISTED

©2013 Legrand 551784. All Rights Reserved 04113 EMA/CGXTP

designed to be better.™



Electrical Wiring Systems

P.O. Box 4822
 Syracuse, NY 13221-4822
 800.776.4035
www.legrand.us/PassandSeymour

570 Applewood Crescent
 Vaughan, Ontario L4K 4B4
 905.738.9195
www.legrand.ca

FOLLOW US

