

# DATA CONNECTIVITY

## PRE-MOLDED WALL PLATES & STRAPS



PART NO.	DESCRIPTION
WMTE14XX	2-Line Wall Mount Telephone Jack for Hanging Phones (4 Conductor Configuration) Colors: I, LA, W
26TE14XX	Decorator 2-Line Telephone Jack (4 Conductor Configuration) Colors: I, LA, W
26TE16XX	Decorator 3-Line Telephone Jack (6 Conductor Configuration) Colors: I, W
26CATVXX	Decorator 1GHz Coaxial Connector Colors: I, LA, W
F9004-XX	5.1 Home Theater Strap Colors: BK, BR, IV, LA, WH
F9005-XX	2-Speaker Connection Strap Colors: BK, BR, IV, LA, WH
F9006-XX	Single Speaker Connection Strap Colors: BK, BR, IV, LA, WH
F9008-XX-V1	5.1 Home Theater Strap with Wall Plate Colors: DM, LA, WH
WP9009-XX-V1	7.1 Home Theater Strap with Wall Plate Colors: BK, BR, IV, LA, WH
WP1014-WH	Cable Access Strap
WP1011-WH	HDMI 2-Port Strap

## PRE-CONFIGURED PLATES & STRAPS



PART NO.	DESCRIPTION
WP3210-XX	1-Port Strap, 1RJ45
WP3211-XX	2-Port Strap Phone/TV
WP3220-XX	2-Port Strap Phone/Data
WP3422-XX	4-Port Strap Phone/Data, TV/AUX

COLORS: BK, LA, WH

### COLOR KEY:



NOTE: The following suffixes should be added to the end of all applicable part numbers. Omit color code to order brown device.

# DATA CONNECTIVITY

## PATCH CABLES



AC6A07-GY-V1



AC3607-BE-V1



AC3507-WH-V1



## CAT 6A PATCH CABLES

PART NO.	DESCRIPTION
AC6A07-GY-V1	7 Foot Cat 6a Patch Cable
AC6A14-GY-V1	14 Foot Cat 6a Patch Cable
AC6A25-GY-V1	25 Foot Cat 6a Patch Cable
AC6A50-GY-V1	50 Foot Cat 6a Patch Cable

- 500MHZ PATCH CABLE FULLY SUPPORTS 10 GIGABIT ETHERNET SPEEDS
- UL VERIFIED TO SUPPORT THE CAT 6a PERFORMANCE PATCH CABLE SPECIFICATION
- SNAGLESS OVERMOLD PREVENTS INSERTION TAB FROM CATCHING ON OTHER CABLES
- 22 AWG STRANDED PATCH CABLE

## CAT 6 PATCH CABLES

PART NO.	DESCRIPTION
AC3607-BE-V1	7 Foot Cat 6 Patch Cable
AC3614-BE-V1	14 Foot Cat 6 Patch Cable
AC3625-BE-V1	25 Foot Cat 6 Patch Cable
AC3650-BE-V1	50 Foot Cat 6 Patch Cable

- 250MHZ PATCH CABLE FULLY SUPPORTS 10 GIGABIT ETHERNET SPEEDS
- UL VERIFIED TO SUPPORT THE CAT 6 PERFORMANCE PATCH CABLE SPECIFICATION
- SNAGLESS OVERMOLD PREVENTS INSERTION TAB FROM CATCHING ON OTHER CABLES
- 22 AWG STRANDED PATCH CABLE

## CAT 5E PATCH CABLES

PART NO.	DESCRIPTION
363201-25-V1	1 Foot Cat 5e Patch Cable
363201-26-V1	2 Foot Cat 5e Patch Cable
AC3503-WH-V1	3 Foot Cat 5e Patch Cable
AC3507-WH-V1	7 Foot Cat 5e Patch Cable
AC3514-WH-V1	14 Foot Cat 5e Patch Cable
AC3525-WH-V1	25 Foot Cat 5e Patch Cable
AC3550-WH-V1	50 Foot Cat 5e Patch Cable

- 100MHZ PATCH CABLE SUPPORTS 10 GIGABIT ETHERNET SPEEDS
- UL VERIFIED TO SUPPORT THE CAT 5e PERFORMANCE PATCH CABLE SPECIFICATION
- SNAGLESS OVERMOLD PREVENTS INSERTION TAB FROM CATCHING ON OTHER CABLES
- 24 AWG STRANDED PATCH CABLE

# DATA CONNECTIVITY

## HDMI CABLES



AC2M01-BK



## HIGH SPEED HDMI CABLES WITH ETHERNET

PART NO.	DESCRIPTION
AC2M00-BK	0.7 Meter HDMI cable w/Ethernet
AC2M01-BK	1 Meter HDMI cable w/Ethernet
AC2M02-BK	2 Meter HDMI cable w/Ethernet
AC2M03-BK	3 Meter HDMI cable w/Ethernet
AC2M04-BK	4 Meter HDMI cable w/Ethernet
AC2M05-BK	5 Meter HDMI cable w/Ethernet
AC2M07-BK	7.5 Meter HDMI cable w/Ethernet
AC2M10-BK	10 Meter HDMI cable w/Ethernet
AC2M15-BK	15 Meter HDMI cable w/Ethernet
AC2M20-BK	20 Meter HDMI cable w/Ethernet
AC2A05-BK	5 Meter HDMI cable w/ Ethernet
AC2A07-BK	7 Meter HDMI cable w/ Ethernet



AC3M01-WH-V1



## HIGH SPEED HDMI WITH ETHERNET SLIMLINE CABLE

PART NO.	DESCRIPTION
AC3M01-WH-V1	1 Meter High Speed HDMI with Ethernet Slimline Cable
AC3M02-WH-V1	2 Meter High Speed HDMI with Ethernet Slimline Cable
AC3M04-WH-V1	4 Meter High Speed HDMI with Ethernet Slimline Cable



AC1030



AC2100



AC2101

## ACCESSORIES

PART NO.	DESCRIPTION
AC1030	<b>HDBaseT HDMI Extender</b>  THE AC1030 KIT EXTENDS HDMI AND INTERNET SIGNALS UP TO 328 FEET USING CAT 5E OR CAT 6 WIRING. IT SUPPORTS 3D VIDEO AND 1080P RESOLUTION, WHILE DUAL IR TARGETS ALLOW THE SOURCE DEVICE TO RECOGNIZE REMOTE COMMANDS AT A SECONDARY LOCATION.  KIT INCLUDES: TRANSMITTER AND RECEIVER UNITS, TWO IR TARGETS AND TWO POWER SUPPLIES.
AC2100	<b>HDMI Repeater</b>  CONNECTS TWO HDMI CABLES AND EXTENDS SIGNAL UP TO 20 FEET.
AC2101	<b>HDMI Hinged Coupler</b>  CONNECTS CABLES TO TIGHT CORNERS.

# DATA CONNECTIVITY

## AUDIO/VIDEO CABLES



## COMPOSITE

PART NO.	DESCRIPTION
AC2006-BK	6 Feet Composite Vid L/R Audio Cable
AC2012-BK	12 Feet Composite Vid L/R Audio Cable

## UNIVERSAL

PART NO.	DESCRIPTION
AC2103-BK	3 Feet Universal 1 Subwoofer Cable
AC2106-BK	6 Feet Universal 1 Subwoofer Cable
AC2112-BK	12 Feet Universal 1 Subwoofer Cable
AC2125-BK	25 Feet Universal 1 Subwoofer Cable
AC2203-BK	3 Feet Universal 2 L/R Audio Cable
AC2206-BK	6 Feet Universal 2 L/R Audio Cable
AC2303-BK	3 Feet Universal 3 Component Video Cable
AC2306-BK	6 Feet Universal 3 Component Video Cable
AC2312-BK	12 Feet Universal 3 Component Video Cable
AC2325-BK	25 Feet Universal 3 Component Video Cable

## TOSLINK

PART NO.	DESCRIPTION
AC2403-BK	3 Feet Toslink w/Mini Audio Cable
AC2406-BK	6 Feet Toslink w/Mini Audio Cable
AC2412-BK	12 Feet Toslink w/Mini Audio Cable
AC2425-BK	25 Feet Toslink w/Mini Audio Cable

## 3.5 MM


PART NO.	DESCRIPTION
AC2501-BK	6 Inches Stereo 3.5 mm Y M/2F Adapter
AC2506-BK	6 Feet Stereo 3.5 mm M/F Audio Cable
AC2512-BK	12 Feet Stereo 3.5 mm M/F Audio Cable
AC2606-BK	6 Feet Stereo 3.5 mm M/M Audio Cable
AC2612-BK	12 Feet Stereo 3.5 mm M/M Audio Cable
AC2625-BK	25 Feet Stereo 3.5 mm M/M Audio Cable

## RCA

PART NO.	DESCRIPTION
AC2701-BK	6 Inches RCA Y M/2F Adapter
AC2702-BK	6 Inches RCA Y F/2M Adapter
AC2704-BK	RCA Coupler Pair
AC2706-BK	6 Feet 3.5 mm to L/R RCA Audio Cable
AC2712-BK	12 Feet 3.5 mm to L/R RCA Audio Cable
AC2725-BK	25 Feet 3.5 mm to L/R RCA Audio Cable

# DATA CONNECTIVITY

## CABLE TIES



PART NO.	DESCRIPTION
AC4000	4.75 Inch, Natural, Cable Ties
AC4001	4.75 Inch, Black, Cable Ties
AC4002	7.5 Inch, Natural, Cable Ties
AC4003	7.5 Inch, Black, Cable Ties
AC4004	11 Inch, Natural, Cable Ties
AC4005	11 Inch, Black, Cable Ties

## PATCH PANELS



PART NO.	DESCRIPTION
24845C5E	Category 5e 24-Port T568A/B Universal Wiring
48845C5E	Category 5e 48-Port T568A/B Universal Wiring
24845CC6	Category 6 24-Port T568A/B Universal Wiring
48845CC6	Category 6 48-Port T568A/B Universal Wiring

- 24 PORT PATCH PANEL USES 1 RACK MOUNT SPACE
- 48 PORT PATCH PANEL USES 2 RACK MOUNT SPACES
- 110 PUNCHDOWN REAR TERMINATION

WP24RM	24 Port Keystone Blank
WP48RM	48 Port Keystone Blank
AC1902	2 U Wall Mount Rack with Extenders
12845C5E89	12-Port T568A/B Universal Wiring
PS665089V	50-Pair 66 Block, Unwired & Mounting Bracket
PS11050KIT4V	50-Pair 110 Kit with Legs

KIT INCLUDES: 110 PUNCH DOWN BLOCK WITH STAND-OFF LEGS, 10 C5 CLIPS, AND LABEL BAR.

## LOW VOLTAGE BRACKETS



PART NO.	DESCRIPTION
AC1009-01	1-Gang, LV Bracket w/Nail, New Const.
AC1009-02	2-Gang, LV Bracket, Face Mount, New Const.
AC1009-11	1-Gang, LV Bracket, Face Mount, New Const.
AC1010-01	1-Gang, LV Bracket, Retrofit
AC1010-02	2-Gang, LV Bracket, Retrofit
AC1010-03	3-Gang, LV Bracket, Retrofit

CRAFTED WITH DURABLE HEAVY-DUTY PLASTIC, ON-Q LV BRACKETS FEATURE AN OPEN BACK AND AN INTEGRATED CABLE MANAGEMENT SYSTEM FOR CLEAN CONNECTIONS AND EASY INSTALLATION.

# INSTALLATION TOOLS & CONNECTORS

## TOOLS



PART NO.	DESCRIPTION
362721-02	RG-6 Coax Stripper
363292-01	Cat 5e Strip and Fit Tool
363293-01	110 Punch Down Tool, Impact
364346-01	Coax Flaring and Insertion Tool
364406-01	High Performance RJ45 Modular Plug Hand Tool
364555-01	EZ RJ-45 Modular Plug Hand Tool
AC3400	Punch & Go Tool  IMPROVES TERMINATION SPEEDS, REDUCES COMPROMISED CONNECTIONS AND INCREASES PRODUCTIVITY OF ANY QUICK CONNECT DATA INSERT.
AC3401	Punch & Go Tool Replacement Blade
AC1018	Radial Taper Compression Tool (use with 364246-01 Coax F Plug)
AC3007	Adjustable Compression Tool
AC4006	Cable Tie Tool

## CONNECTORS



PART NO.	DESCRIPTION
364246-01	360 Conical Coax F Plug
364405-01	High Performance RJ45 Modular Plugs (25 Pack)
364554-01	EZ-RJ45 Modular Cat 5e Plug
AC2006	EZ-RJ45 Modular Cat 6 Plug
WP3483-01	Banana Plugs (pair)
AC3001-10	Compression RG6U/Quad F Plug, 10 Pack
AC3002-10	Compression RG6U/Quad 3 GHz F Jack, 10 Pack
AC3003-10	Compression RG6U/Quad Shield BNC Plug, 10 Pack
AC3004-10	Compression RG6U/Quad Shield RCA Plug, 10 Pack (50 Pack also available, AC3004-50)
AC3005-10	Compression RG6U/Quad Shield Right Angle RCA Plug
AC3006-10	Nickle F-81 1 GHz Coupler, 10 Pack (50 Pack also available, AC3006-50)
AC3008-10	Compression RG6U/Quad F Plug 10 Pack (50 Pack also available, AC3008-50)

# POWER MANAGEMENT

## POWER SUPPLIES



PW7760



PW7725



PW1030



PW1060



PW1120



PW1240



PW1248

PART NO.	DESCRIPTION
PW7760	12VDC, 18W Power Supply
PW7725	12VDC, 30W Power Supply
PW1030	24VDC, 30W Power Supply
PW1060	24VDC, 60W Power Supply
PW1120	24VDC, 120W Power Supply Kit
	KIT INCLUDES: TWO 24VDC, 60W POWER SUPPLIES (PW1060), ONE MOUNTING BRACKET (PW1006), ONE CUSTOM MOUNTING BRACKET, AND VELCRO STRIPS
PW1240	24VDC, 240W Power Supply Kit
	KIT INCLUDES: FOUR 24VDC, 60W POWER SUPPLIES (PW1060), TWO MOUNTING BRACKETS (PW1006), ONE CUSTOM POWER STRIP, AND VELCRO STRAPS
PW1248	48VDC, 100W Power Supply



364569-02-V1



F7526



PW1006

## ACCESSORIES

PART NO.	DESCRIPTION
364569-02-V1	Surge Protected Duplex Power Kit
F7526	Duplex Power Kit
	KIT INCLUDES: A SURGE PROTECTED DUPLEX OUTLET, METAL JUNCTION BOX AND A FACEPLATE KIT.
PW1006	Twin Power Supply Bracket

## POWER MODULES



PW1012



PW1013



PW1020



AC1031

PART NO.	DESCRIPTION
PW1012	Universal Power Distribution Module
PW1013	Intuity Bridge Power Module
PW1020	Digital Audio Power Distribution Module
AC1031	Enclosure Power Strip Module, Half Width

# VIDEO & VOICE DISTRIBUTION

## VOICE & VIDEO MODULES

### COMBO MODULES

DESCRIPTION	Basic 6x4 Combo (110 Punchdown)	10x8 Combo with RJ31X (RJ45)	10x8 Combo with RJ31X (110 Punchdown)	10x8 Combo with RJ31X MoCA Optimized
				
PART NO.	364400-04	CO1045	CO1110	CO2110-V1
Telecom Outlets	6	10	10	10
Video Outlets	4	8	8	8
Telecom Connections	110 Punchdown	RJ45	110 Punchdown	110 Punchdown
RJ31X Line Seizure	N	Y	Y	Y
Bandwidth	1 GHz	1 GHz	1 GHz	1 GHz
Dimensions	5 1/8" x 6 1/2"	5 1/8" x 6 1/2"	5 1/8" x 6 1/2"	5 1/8" x 6 1/2"

### VOICE MODULES

PART NO.	DESCRIPTION
TM1110	10-Way IDC Telephone Module with RJ31X
TM1045	10-Way RJ45 Telephone Module with RJ31X
1267062-01-V1	6-Way Basic Telecom Module with RJ31X

### VIDEO MODULES

PART NO.	DESCRIPTION
VM1000	1x4 Enhanced Passive Video Splitter/Combiner
VM1002	1x8 Enhanced Passive Video Splitter/Combiner



TM1110



TM1045



1267062-01-V1



VM1000



VM1002





# NETWORKING

## WIRED NETWORKS



DA1008



DA1458




DA1054



363486-01



AC1000



AC1001



AC1012



AC1013



AC1014



AC1015



DA2400



DA2401



AC1025



DA1104



DA1101



DA2131-V1

## ROUTERS & SWITCHES

PART NO.	DESCRIPTION
DA1008	8-Port Gigabit Switch
DA1458	8-Port Gigabit Switch with 4-Port PoE Injector
DA1054	4-Port Gigabit Ethernet Router/Switch

## MODULES

PART NO.	DESCRIPTION
363486-01	8-Port Cat 5e Network Interface Module
AC1000	6-Port Cat 5e Network Interface Module
AC1001	6-Port Network Interface Module (Unpopulated)
AC1012	6-Port Cat 5e Network Interface Module
AC1013	6-Port Cat 6 Network Interface Module
AC1014	12-Port Cat 5e Network Interface Module
AC1015	12-Port Cat 6 Network Interface Module

## POWER OVER ETHERNET

PART NO.	DESCRIPTION
DA2400	802.3af 4-Port PoE Injector
DA2401	802.3at 4-Port High Performance PoE Injector
AC1025	Power Over Ethernet Mounting Plate

## WIRELESS NETWORKS

PART NO.	DESCRIPTION
DA1104	802.11ac Low Profile Wireless Access Point
DA1101	802.11n In-Wall/Ceiling Wireless Access Point
DA2131-V1	802.11n Outdoor Wireless Access Point

# RESOURCES & SUPPORT

## TECH SUPPORT

Need help on the job? Legrand's expert team of support specialists are available Monday through Friday, from 8:30 am to 6:30 pm Eastern Time, to answer your product or installation questions. The staff can be reached during these standard hours by any of the below options:

**Phone:** 800.223.4162, Option #3, then Option #2

**Email:** [technical.support-hs@legrand.us](mailto:technical.support-hs@legrand.us)

**Live Chat:** available through the [www.legrand.us](http://www.legrand.us) website

## CUSTOMER SERVICE

Friendly and knowledgeable, our team can handle a wide variety of needs and requests – from order processing to system registration – and is available Monday through Friday, from 9 am to 6 pm Eastern Time.

**Phone:** 844.334.8044

**Email (general inquiries):** [customer.support.lv@legrand.us](mailto:customer.support.lv@legrand.us)

**Email (orders):** [orders.lv@legrand.us](mailto:orders.lv@legrand.us)

## TRAINING

Knowledge is power, and Legrand offers a wealth of product, industry, and installation knowledge through our on-site and online courses.

Visit the Legrand University at <http://go.bluevolt.com/Legrand/Home/> for convenient online courses you can complete at your own pace, recorded past webinars to catch anything you may have missed, as well as a complete schedule of upcoming FREE webinars.

designed to be better™



301 Fulling Mill Road, Suite G  
Middletown, PA 17057  
(800) 321-2343  
[www.legrand.us/onq](http://www.legrand.us/onq)

570 Applewood Crescent  
Vaughan, Ontario L4K 4B4  
905.738.9195  
[www.legrand.ca](http://www.legrand.ca)

Follow Us

