SWITCHES

Decorator & Specification Grade Momentary & Maintained Contact Switches

15A, 120 & 120/277VAC





TM870STMLACC6 Contact

Features

- Designer-style satin-finish rocker.
- High-impact resistant thermoplastic construction.
- External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.
- Push wire #14 AWG.

Narrow back body leaves more room for wires in the box.
Extra-long, through-body strap eliminates

3.812'

- floating installations and imperfect applications.
- Smooth, quiet paddle action.

Maintained

Contact

- Easy-access green hex head ground screw.
- Tri-drive ground, terminal and mounting screws.

	RATING			3rd PARTY COMPLIANCE				
				(h)	SF-			
CATALOG NUMBER	Α.	VAC	COLOR	UL20	C22.2 111			
SINGLE POLE DECORATOR MOMENTARY CONTACT SWITCHES								
TM870STMWCC6	15	120/277	White	•	•			
TM870STMBKCC6	15	120/277	Black	•	•			
M870STMLACC6	15	120/277	Light Almond	•	•			

Features

- Unique "Up/Down" switches match the look and feel of standard decorator switches.
- Impact-resistant face and body.
- Side and external screw-pressure-plate back wire accepts #12 and #14 AWG.
- All screws are tri-drive.
- Full wraparound heavy-gauge steel strap is plated for corrosion resistance and features lock-in tabs.
- Patent-pending split circuit tab easily accessible, and can be reinstalled without a tool.

	RATING			3rd PARTY COMPLIANCE						
				(h)	(h)	(h)				
CATALOG NUMBER	Α.	VAC	COLOR	cULus	UL20	UL508				
SPECIFICATION GRADE DOUBLE THROW MOMENTARY CONTACT SWITCHES										
TM811DTM0I	15	120	lvory	•		•				
TM811DTMOW	15	120	White	•		•				
TM811DTM0BK	15	120	Black	•		•				
TM811DTMOLA	15	120	Light Almond	•		•				
SPECIFICATION GRADE DOUBLE THROW MAINTAINED CONTACT SWITCHES										
TM811DTMAI	15	120	lvory	•	•					
TM811DTMAW	15	120	White	•	•					
TM811DTMABK	15	120	Black	•	•					
TM811DTMALA	15	120	Light Almond	•	•					