


SUPERIOR INFRASTRUCTURE SOLUTIONS



CONNECTIVITY



As the industry leader in structured wiring, Legrand provides the proven, practical solutions preferred by installers and major home builders across the country. Our comprehensive product offering — which includes On-Q wall plates, jacks, straps, tools, modules and enclosures — simplifies installations and reduces time on site. We specialize in meeting the right specifications for any project — residential or light commercial — with solutions that exceed your needs. From single-family homes to apartments, townhomes to condominiums, Legrand has the professional answer for any project.

HDMI

This full line of High-Speed HDMI with Ethernet products — which includes cables, couplers, repeaters and extenders — delivers an unparalleled HD audio and video experience. All of our HDMI cables are CL-3 and in-wall UL-rated.





WALL PLATES & INSERTS

Our line of Keystone wall plates; Cat 5e, Cat 6, Cat 6a, F Connectors; speaker binding posts; and RCA inserts provides flexible setup options anywhere in the home.

DECORATOR STRAPS

We offer a series of pre-configured outlet straps for data, phone, video and home theater applications. Add a home theater strap to enable HD audio and video with a few simple connections, or quickly wire a home office using our pre-configured outlet straps that combine phone, data and video into a single decorator opening.

ENCLOSURES

Our durable enclosures range in size from 12 to 42 inches to suit any installation. Every enclosure is made in the USA and is compatible with all major module mounting schemes. They offer three 2.5 inch top openings for high capacity projects, as well as side lances and tabs for greater flexibility during installation. Available with hinged or screw-on doors, an On-Q enclosure is the easy choice for professional projects.



HDMI

AC2MXX-BK High-Speed HDMI Cables with Ethernet



AC2M01-BK

PART NO.	DESCRIPTION
AC2M00-BK	0.7 Meter High-Speed HDMI cable w/Ethernet
AC2M01-BK	1 Meter High-Speed HDMI cable w/Ethernet
AC2M02-BK	2 Meter High-Speed HDMI cable w/Ethernet
AC2M03-BK	3 Meter High-Speed HDMI cable w/Ethernet
AC2M04-BK	4 Meter High-Speed HDMI cable w/Ethernet
AC2M05-BK	5 Meter High-Speed HDMI cable w/Ethernet
AC2M07-BK	7.5 Meter High-Speed HDMI cable w/Ethernet
AC2M10-BK	10 Meter High-Speed HDMI cable w/Ethernet
AC2M15-BK	15 Meter High-Speed HDMI cable w/Ethernet
AC2M20-BK	20 Meter High-Speed HDMI cable w/Ethernet

- DELIVERS UNCOMPRESSED HD VIDEO AND DIGITAL AUDIO IN A SINGLE CABLE
- AUDIO RETURN CHANNEL (ARC) AND HDMI ETHERNET CHANNEL (HEC) CAPABLE
- COMPATIBLE WITH HDTVS, DVD/BLU-RAY PLAYERS, CABLE & SATELLITE SET TOP BOXES, AND GAMING CONSOLES
- GOLD-PLATED CONNECTORS WITH INDIVIDUALLY SHIELDED CONDUCTORS ENSURE MAXIMUM RESOLUTION

AC3MXX-WH-V1 High-Speed HDMI with Ethernet Slimline Cables



AC3MXX-WH-v1

PART NO.	DESCRIPTION
AC3M01-WH-V1	1 Meter High-Speed HDMI w/ Ethernet Slimline Cable
AC3M02-WH-V1	2 Meter High-Speed HDMI w/ Ethernet Slimline Cable
AC3M04-WH-V1	4 Meter High-Speed HDMI w/ Ethernet Slimline Cable


- 75% THINNER THAN REGULAR HDMI CABLES DELIVERS UNCOMPRESSED HD VIDEO AND DIGITAL AUDIO IN A SINGLE CABLE
- AUDIO RETURN CHANNEL & HDMI ETHERNET CHANNEL (HEC) CAPABLE
- REDUCED WEIGHT ALLOWS FOR A MORE SECURE CONNECTION TO TELEVISIONS AND OTHER COMPONENTS
- REDUCED CABLE PROFILE FOR A PROFESSIONAL UNCLUTTERED LOOK
- UTILIZES REDMERE™ SYNERCHIP FOR HIGH BANDWIDTH SUPPORT OVER DISTANCE

HDMI

HDBaseT HDMI Extender

NEW!


PART NO.	DESCRIPTION
AC1030	HDBaseT HDMI Extender
	<ul style="list-style-type: none"> THE AC1030 KIT EXTENDS HDMI AND INTERNET SIGNALS UP TO 328 FEET USING CAT 5 OR CAT 6 WIRING. IT SUPPORTS 3D VIDEO AND 1080P RESOLUTION, WHILE DUAL IR TARGETS ALLOW THE SOURCE DEVICE TO RECOGNIZE REMOTE COMMANDS AT A SECONDARY LOCATION.



HDMI Accessories

NEW!


WP1011-WH



AC2100



AC2101

PART NO.	DESCRIPTION
WP1011-XX	Pre-Configured HDMI 2-Port Strap Colors: BK, LA, WH
AC2100	HDMI Repeater <ul style="list-style-type: none"> CONNECTS TWO HDMI HIGH-SPEED WITH ETHERNET CABLES & EXTENDS ETHERNET SIGNAL UP TO 20 FEET
AC2101	HDMI Hinged Coupler <ul style="list-style-type: none"> REDUCES CABLE BENDING FOR SUPERIOR ORGANIZATION



WALL PLATES & INSERTS

KEYSTONE WALL PLATES



WP3401-WH*



WP3402-WH*




WP3403-WH



WP3404-WH



WP3406-WH



WP3212-WH



WP1194-WH

*Available in packs of 25

PART NO.	DESCRIPTION
WP3401-XX (KTPD1XX)	1-Gang, 1-Port Wall Plate 25 Count Bulk Pack in WH (W) or LA (WP3401-XX-25)
WP3402-XX (KTPD2XX)	1-Gang, 2-Port Wall Plate 25 Count Bulk Pack in WH (W) or LA (WP3402-XX-25)
WP3403-XX (KTPD3XX)	1-Gang, 3-Port Wall Plate
WP3404-XX (KTPD4XX)	1-Gang, 4-Port Wall Plate
WP3406-XX (KTPD6XX)	1-Gang, 6-Port Wall Plate
WP3212-XX	2-Gang, 12-Port Wall Plate Colors: IV, LA and WH
WP1194-XX	1-Gang, Blank Wall Plate

COLORS: BK, BR, IV (I), LA, WH (W)
DIMENSIONS: 1-GANG: 2.9375" x 4.6875" 2-GANG: 4.75" x 4.6875"

KEYSTONE LABELED Wall Plates

PART NO.	DESCRIPTION
KTPDL1XX	1-Port Keystone Labeled Wall Plate
KTPDL2XX	2-Port Keystone Labeled Wall Plate
KTPDL3XX	3-Port Keystone Labeled Wall Plate
KTPDL4XX	4-Port Keystone Labeled Wall Plate
KTPDL6XX	6-Port Keystone Labeled Wall Plate

COLORS: I, LA, W

DIMENSIONS: 1-GANG: 2.9375" x 4.6875" 2-GANG: 4.75" x 4.6875"

OVERSIZED WALL PLATES



WP3301-WH



WP3302-WH



WP3303-WH



WP3304-WH



WP3306-WH



WP3300-WH

PART NO.	DESCRIPTION
WP3301-XX	1-Gang, 1-Port Oversized Wall Plate
WP3302-XX	1-Gang, 2-Port Oversized Wall Plate
WP3303-XX	1-Gang, 3-Port Oversized Wall Plate
WP3304-XX	1-Gang, 4-Port Oversized Wall Plate
WP3306-XX	1-Gang, 6-Port Oversized Wall Plate
WP3300-XX	1-Gang, Blank Oversized Wall Plate

COLORS: WH, LA
DIMENSIONS: 1-GANG: 3.3125" x 5.0625" 2-GANG: 5.125" x 5.0625"
3-GANG: 6.9375" x 5.0625" 4-GANG: 8.75" x 5.0625"

COLOR OPTIONS



WALL PLATES & INSERTS

DECORATOR WALL PLATES



TP13W



TP26W



TP262W



TP263W



TP264W

PART NO.	DESCRIPTION
TP13XX [†] (WP1194-XX)	1-Gang Blank Wall Plate
TP26XX [†] (WP1205-XX)	1-Gang Decorator Wall Plate
TP262XX [†] (WP1207-XX)	2-Gang Decorator Wall Plate
TP263XX [†] (WP1208-XX)	3-Gang Decorator Wall Plate
TP264XX [†]	4-Gang Decorator Wall Plate

COLORS:

BK, BR, IV (I), LA, WH (W)

DIMENSIONS:

1-GANG: 2.9375" x 4.6875" 2-GANG: 4.75" x 4.6875"

JUMBO DECORATOR Wall Plates

PART NO.	DESCRIPTION
TPJ13XX	Jumbo 1-Gang Blank Wall Plate
TPJ26XX	Jumbo 1-Gang Wall Plate
TPJ262XX	Jumbo 2-Gang Wall Plate
TPJ263XX	Jumbo 3-Gang Wall Plate

COLORS:

BK, I, LA, W

DIMENSIONS:

1-GANG: 3.3125" X 5.0625", 2-GANG: 5.125" X 5.0625", 3-GANG: 6.9375" X 5.0625"

LOW VOLTAGE BRACKETS



AC1009-01



AC1009-02



AC1009-11



AC1010-01



AC1010-02



AC1010-03

PART NO.	DESCRIPTION
AC1009-01	1-Gang, LV Bracket w/Nail, New Construction
AC1009-02	2-Gang, LV Bracket, Face Mount, New
AC1009-11	1-Gang, LV Bracket, Face Mount, New
AC1010-01	1-Gang, LV Bracket, Retrofit
AC1010-02	2-Gang, LV Bracket, Retrofit
AC1010-03	3-Gang, LV Bracket, Retrofit

CRAFTED WITH DURABLE HEAVY-DUTY PLASTIC, ON-Q LV BRACKETS FEATURE AN OPEN BACK AND AN INTEGRATED CABLE MANAGEMENT SYSTEM FOR CLEAN CONNECTIONS AND EASY INSTALLATION

COLOR OPTIONS



BK

BR

IV (I)

LA

WH (W)

WALL PLATES & INSERTS

TELEPHONE AND DATA Keystone Inserts



WP3475-WH*



WP3476-WH



WP346A-WH



WP3450-WH*



WP3460-WH



WP3458-WH



WP3451-WH



WP3425-WH



WP3550-WH



WP3560-WH

* Available in white, light almond, and blue in packs of 50

PART NO.	DESCRIPTION
WP3475-XX	Cat 5e Quick Connect RJ45 Keystone Connector Colors: BE, BK, BR, GY, GN, IV, LA, OR, RE, WH, YE
WP3476-XX	Cat 6 Quick Connect RJ45 Keystone Connector Colors: BE, BK, BR, GY, IV, LA, OR, RE, WH
WP346A-XX	Cat 6a Quick Connect RJ45 Keystone Connector Colors: BE, BK, BR, GY, GN, IV, LA, OR, RE, WH, YE ... TERMINATE ALL WIRES AT ONCE USING THE AC3400 PUNCH & GO TOOL WITH ANY QUICK CONNECT INSERT
WP3450-XX (KS58ABXX)†	Cat 5e RJ45 Keystone Connector Colors: BE (BL), BK, BR, GY (GRY), IV (I), LA, OR, RE (RED), WH (WH)
WP3460-XX (KS68ABXX)†	Cat 6 RJ45 Keystone Connector Colors: BE (BL), BK, BR, GY (GRY), IV (I), LA, OR, RE (RED), WH (WH)
WP3458-XX	Cat 5e Keyed RJ45 Keystone Connector Colors: BK, BR, IV, LA, WH
WP3451-XX (KS888XX)	Cat 5e RJ45 Keystone Coupler Colors: BK, WH (W)
WP3425-XX (KS6UXX)†	RJ25 6P6C Keystone Connector Colors: BK, BR, IV (I), LA, WH (W)
WP3550-XX	Snap & Go Cat 5e Keystone Connector Colors: BE, BK, BR, GY, IV, LA, OR, RE, WH
WP3560-XX	Snap & Go Cat 6 Keystone Connector Colors: BE, BK, BR, GY, IV, LA, OR, RE, WH

VIDEO INSERTS




WP3479-WH*



WP3480-WH



WP3481-WH*



WP3482-WH



WP1234-WH



WP3455-WH



KSBNCW



KSSVW

*Available in packs of 50.

PART NO.	DESCRIPTION
WP3479-XX	Non-Recessed Coax Keystone F Connector (1 GHz) 50 Count Bulk Pack in WH or LA (WP3479-XX-50)
WP3480-XX	Recessed Gold F Connector (3GHz)
WP3481-XX (KSFFXX)	Recessed Nickle F Connector (3GHz) 50 Count Bulk Pack in WH (WP3481-WH-50)
WP3482-XX (KSFFSTXX)	Recessed Self-Terminating Keystone F Connector (1 GHz)
WP1234-XX	HDMI Keystone Insert/Coupler
WP3455-XX (KSBL10XX)†	Blank Keystone Insert Colors: BK, BR, IV (I), LA, WH (W)
KSBNCXX	Keystone BNC-to-BNC Connector
KSSVXX	Keystone S-Video-to-110 Termination Colors: I, LA, W

COLOR OPTIONS



WALL PLATES & INSERTS

RCA TO F CONNECTORS



WP3461-WH



WP3462-WH



WP3463-WH



WP3464-WH



WP3465-WH



WP3466-WH

PART NO.	DESCRIPTION
WP3461-XX	White Keystone RCA to F Connector Connector Application: Left/Mono
WP3462-XX (KSRCAFX) [†]	Red Keystone RCA to F Connector Connector Application: Right
WP3463-XX	Green Keystone RCA to F Connector Connector Application: Center
WP3464-XX	Blue Keystone RCA to F Connector Connector Application: Left Surround
WP3465-XX	Yellow Keystone RCA to F Connector Connector Application: Composite Video
WP3466-XX	Purple Keystone RCA to F Connector Connector Application: Subwoofer

COLORS:

BK, BR, IV (I), LA, WH (W)

MULTIMEDIA INSERTS



KSSCW



KSSTW



WP3457-WH



WP3456-WH

PART NO.	DESCRIPTION
KSSCXX	Keystone SC Multimode, Phosphor Bronze Sleeve Colors: I, LA, W
KSSTXX	Keystone ST Multimode, Phosphor Bronze Sleeve Colors: I, LA, W
WP3457-XX (KS2BPXX) [†]	Audio Keystone Binding Post - Pair Colors: BK, BR, IV (I), LA, WH (W)
WP3456-XX	Speaker Pair Insert Colors: BK, BR, IV, LA, WH

RCA TO RCA INSERTS



KSRCAYW



KSRCARW



KSRCABW



KSRCABEW



KSRCAGNW

PART NO.	DESCRIPTION
KSRCAYXX	Keystone RCA to RCA (Yellow Insulator) Colors: I, LA, W
KSRCARXX	Keystone RCA to RCA (Red Insulator) Colors: I, LA, W
KSRCABXX	Keystone RCA to RCA (Black Insulator) Colors: I, LA, W
KSRCABEXX	Keystone RCA to RCA (Blue Insulator) Colors: I, LA, W
KSRCAGNXX	Keystone RCA to RCA (Green Insulator) Colors: I, LA, W

COLOR OPTIONS



BK

BR

IV (I)

LA

WH (W)

WALL PLATES & INSERTS

CAT 5e PATCH CABLES



363201-2X-V1
AC35XX-WH-V1



PART NO.	DESCRIPTION
363201-26-V1	1 Foot Cat 5e Patch Cable
363201-25-V1	2 Foot Cat 5e Patch Cable
AC3503-WH-V1	3 Foot Cat 5e Patch Cable
AC3507-WH-V1	7 Foot Cat 5e Patch Cable
AC3514-WH-V1	14 Foot Cat 5e Patch Cable
AC3525-WH-V1	25 Foot Cat 5e Patch Cable
AC3550-WH-V1	50 Foot Cat 5e Patch Cable
	<ul style="list-style-type: none"> • 100MHZ RATED PATCH CABLE • UL VERIFIED TO SUPPORT THE CAT 5e PERFORMANCE PATCH CABLE SPECIFICATION • SNAGLESS OVERMOLD PREVENTS INSERTION TAB FROM CATCHING ON OTHER CABLES • 24 AWG STRANDED PATCH CABLE • AVAILABLE IN WHITE

CAT 6 PATCH CABLES



AC36XX-BE-V1



PART NO.	DESCRIPTION	NEW!
AC3607-BE-V1	7 Foot Cat 6 Patch Cable	
AC3614-BE-V1	14 Foot Cat 6 Patch Cable	
AC3625-BE-V1	25 Foot Cat 6 Patch Cable	
AC3650-BE-V1	50 Foot Cat 6 Patch Cable	
	<ul style="list-style-type: none"> • 250MHZ RATED PATCH CABLE • UL VERIFIED TO SUPPORT THE CAT 6 PERFORMANCE PATCH CABLE SPECIFICATION • SNAGLESS OVERMOLD PREVENTS INSERTION TAB FROM CATCHING ON OTHER CABLES • 22 AWG STRANDED PATCH CABLE • AVAILABLE IN BLUE 	

CAT 6a PATCH CABLES



AC6AXX-GY-V1



PART NO.	DESCRIPTION	NEW!
AC6A07-GY-V1	7 Foot Cat 6a Patch Cable	
AC6A14-GY-V1	14 Foot Cat 6a Patch Cable	
AC6A25-GY-V1	25 Foot Cat 6a Patch Cable	
AC6A50-GY-V1	50 Foot Cat 6a Patch Cable	
	<ul style="list-style-type: none"> • 500MHZ RATED PATCH CABLE • UL VERIFIED TO SUPPORT THE CAT 6a PERFORMANCE PATCH CABLE SPECIFICATION • SNAGLESS OVERMOLD PREVENTS INSERTION TAB FROM CATCHING ON OTHER CABLES • 22 AWG STRANDED PATCH CABLE • AVAILABLE IN GRAY 	