

**Datasheet**

Art.No. 70.325.0628.0

Bottom BAS GUT GP 6 50 A

revos BASIC 500V size 6 open-bottom base, with cover, single locking lever



Art.No.	70.325.0628.0
EAN	4015573220188
Order unit	1 pieces

**Approvals**



**Technical data**

**General**

Housing material	Aluminium
Colour	Grey
Surface	With powder coating
Degree of protection (IP)	IP65
UV resistant	Yes
Inflammability class of insulation material acc. with UL94	Other
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

**Model**

DIN-size	6
Model	Equipment mounted (feed-through)
Locking mechanism	Single locking lever
Cable entry	None
Type of cable	None
With cable screw gland	No
Hinged lid	Yes
EMC-version	No