

Datasheet

Art.No. 76.320.0729.0

Bottom MIN GUT GA 7 25 Z

revos MINI size 3 open-bottom base single locking lever, metal housing



Art.No.	76.320.0729.0
EAN	4015573563247
Order unit	10 pieces

Approvals

Technical data

**General**

Housing material	Cast zinc
Colour	Grey
Surface	With powder coating
Degree of protection (IP)	IP54
UV resistant	Yes
Inflammability class of insulation material acc. with UL94	Other
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

**Model**

DIN-size	3
Model	Equipment mounted (feed-through)
Locking mechanism	Single locking lever
Cable entry	None
Type of cable	None
With cable screw gland	No
Hinged lid	No
EMC-version	No