

Datasheet

Art.No. 81.000.6110.0

Switched-mode power supply WIPOS P1 24-1.25

wipos switched-mode power supply, nominal voltage: 24 V DC / 1,25A (setting range 24-28 V DC), sustained short-circuit protection, input voltage range: 85-264 V AC / 90-375V DC, single phase, W x H x D: 40,5 x 88,5 x 115 mm



Art.No.	81.000.6110.0
EAN	4049088037443
Order unit	1 pieces

Approvals



Technical data

General

Connection type	Screw connection
Modular version	No
Mounting type, other	No
Mounting type, wall mounting	No
Rail mounting possible	Yes

Technical data

Power consumption	42 VA
Type of voltage (input voltage)	
Power output	35 W
Type of output voltage	DC
Output voltage stabilized	Yes
Min. output voltage	24 V
Max. output voltage	28 V
Output current	1.25 A
Input voltage AC min.	85 V
Input voltage AC max.	264 V
Input voltage DC min.	90 V
Input voltage DC max.	375 V

Dimensions

Depth	115 mm
Width	40.5 mm

Height	90 mm
--------	-------