

Datasheet

Art.No. 80.010.4525.0


Relay module FLARE MOVE115V-1W-6A

"standard relay module flare MOVE 115V-1W-6A, width 6,2 mm, plugable, nominal operating voltage 115V AC/DC, 1 change-over contact 25 0V AC / 6A, AgSnO₂;"



Art.No.	80.010.4525.0
EAN	4015573647688
Order unit	10 pieces

Approvals



Technical data

General

Connection type	Screw connection
Number of change-over contacts	1
Detachable clamps	No
Drive, polarization	Polarity free
Drive, function	Mono stable
Forced-guided contacts	No
Complete with socket	Yes
Degree of protection (IP)	IP20

Technical data

Type of excitation	
Rated frequency, auxiliary-/control circuit	50 - 60
Min. rated frequency, auxiliary/control current circuit	50 Hz
Max. rated frequency, auxiliary/control current circuit	60 Hz
Nominal voltage DC	115 V
Lower nominal voltage DC	92 V
Upper nominal voltage DC	126.5 V

Dimensions

Depth	76 mm
Width	6.2 mm
Height	88 mm