


**Datasheet**

Art.No. Z7.409.8956.0

Cover BAS AD DA 24 FS

Protective cover with tether cord without locking levers, without gasket size 24



|            |               |
|------------|---------------|
| Art.No.    | Z7.409.8956.0 |
| EAN        | 4015573159129 |
| Order unit | 10 pieces     |

**Approvals**

**Technical data**

**General**

|  |           |
|--|-----------|
| Degree of protection (IP)                                  | IP65      |
| Inflammability class of insulation material acc. with UL94 | V0        |
| Housing material   | Plastic   |
| Surface  | Untreated |
| Colour   | Grey      |
| Operating temperature range min.                           | -40 °C    |
| Operating temperature range max.                           | 120 °C    |

**Model**

|                           |                       |
|---------------------------|-----------------------|
| DIN-size                  | 24                    |
| Interlock                 | No                    |
| Locking mechanism         | Double locking levers |
| Material locking lever    | None                  |
| Cover attachment clamping | No                    |
| With sealing              | No                    |
| With tether cord          | Yes                   |
| With loop                 | Yes                   |
| With ring lug             | No                    |