

Datasheet

Art.No. 80.010.4000.0

Relay module FLARE-24DC-1W-250V6A

flare relays, output, 1 change-over contact, width 6,2 mm, screw clamp terminal, input data: 24 V DC / 14mA, output: 250 V AC/6 A (Note: With jumpers, the negative pole of the control side can be bridged to the neighboring pole), if needed they have to be ordered separately).



Art.No.	80.010.4000.0
EAN	4015573418141
Order unit	10 pieces

Approvals



Technical data

General

Connection type	Screw connection
Number of change-over contacts	1
Detachable clamps	No
Drive, polarization	Polarity free
Drive, function	Mono stable
Forced-guided contacts	No
Complete with socket	Yes
Degree of protection (IP)	IP20

Technical data

Type of excitation	
Nominal voltage DC	24 V
Lower nominal voltage DC	19.2 V
Upper nominal voltage DC	30 V

Dimensions

Depth	70 mm
Width	6.2 mm
Height	89 mm