

Datasheet

Art.No. 70.300.1040.0

Female insert BAS BUS 10 2,5 50

revos BASIC 500V 10 pole + ground, female insert 500V/16A with wire protection, Sn screw connection



Art.No.	70.300.1040.0
EAN	4015573219601
Order unit	10 pieces

Approvals



Technical data

General

Model	Female insert
Inflammability class of insulation material acc. with UL94	V0
Colour	Grey
Mating cycles	200
Pollution degree	3
Modular version	No
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

Connection Data

Connection type	Screw connection
Number of poles	10
Plus switching contacts	0
Number of pole for rated current 2	0
Number of pole for rated current 3	0
Total number of poles (without ground contact)	10
With wire protection	Yes
Min. conductor diameter rigid (solid/stranded)	0.5
Max. conductor diameter rigid (solid/stranded)	2.5
Protective contact	Yes

Technical Data UL/CSA

Rated voltage according to UL/CSA	600
-----------------------------------	-----

Rated current according UL	16
Rated current according CSA	16
Min. conductor cross section flexible wire	0.5
Max. conductor cross section flexible wire	2.5
Conductor cross section flexible AWG wire	22-14 AWG

Model

With housing	No
--------------	----

Contacts

Contact material	Copper alloy
Surface	Tin-plated
Contact resistance	1.5 mOhm
Wire strip length	7 mm

Screws head design/recomm. Torque

Mounting screws	H1/0.5-0.7 Nm
Clamping screws	H1/0.5-0.7 Nm
Ground conductor screws	H2/1.2-1.6 Nm

Technical Data DIN EN 61984

Nominal voltage	500
Rated voltage face/ground	500
Nominal current	16
Rated impulse voltage	6 kV