

Datasheet

Art.No. 57.016.5055.0

Feed-through terminal

Feed-through DIN rail terminal block with double screw connection for mounting on TS 35 and TS 32, nominal cross section 16 mm², width 10 mm, color gray



Art.No.	57.016.5055.0
EAN	4049088148590
Order unit	1 [undefined]

Approvals

Technical data

General

Nominal cross section	16 mm ²
Colour	Grey
Number of levels	1
Number of clamp positions per level	2
Width/grid dimension	12 mm
Insulating housing	PA666
Inflammability class of insulation material acc. with UL94	V0
Explosion-tested version "Ex e"	Yes
Mounting method	DIN rail (top hat rail)/G-rail
Terminal blocks for electrical installations	No

Technical data

Rated current	76 A
Rated voltage	800 V
Rated impulse voltage	8 kV
Pollution degree	3
Closing plate required	Yes
Type of insulation material	Thermoplastic
Length	68 mm

Connection Data

Connection type 1	Screw connection
Connection type 2	Screw connection
Minimum cross section solid	1.5 mm ²
Maximum cross section solid	10 mm ²
Minimum cross section fine stranded	1.5 mm ²

Maximum cross section fine stranded	16 mm ²
Minimum cross section stranded	16 mm ²
Maximum cross section stranded	25 mm ²
Wire strip length	18 mm
Torque conductor mounting	2 Nm

Technical Data UL/CSA

Voltage CSA	600 V
Current CSA	65 A