

## Datasheet

Art.No. 70.352.1035.0

Hood BAS GOT GC 10 M20 50 A0

revos BASIC 500V size 10 hood with cable gland M20, top cable entry, double locking lever



Art.No.	70.352.1035.0
EAN	4015573616905
Order unit	1 pieces

## Approvals



## Technical data

### General

Nominal voltage	500
Housing material	Aluminium
Colour	Grey
Surface	With powder coating
Degree of protection (IP)	IP54
UV resistant	Yes
Inflammability class of insulation material acc. with UL94	Other
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

### Model

DIN-size	10
Model	male
Locking mechanism	Double locking levers
Cable entry	Above
Type of cable	Gland nut
With cable screw gland	Yes
Thread size M	20
Hinged lid	No
EMC-version	No