

## Datasheet

Art.No. 76.352.0736.0

Hood MIN GOT GB 7 M20 25 Z0

revos MINI size 3 hood with cable gland M20, top cable entry, single locking lever, metal housing



Art.No.	76.352.0736.0
EAN	4015573651159
Order unit	10 pieces

## Approvals

## Technical data

### General

Housing material	Cast zinc
Colour	Grey
Surface	With powder coating
Degree of protection (IP)	IP54
UV resistant	Yes
Inflammability class of insulation material acc. with UL94	Other
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

### Model

DIN-size	3
Model	male
Locking mechanism	Single locking lever
Cable entry	Above
Type of cable	Gland nut
With cable screw gland	Yes
Thread size M	20
Hinged lid	No
EMC-version	No