



2.5 mm²/5 mm wide

4 mm²/6 mm wide

**10 mm²/10 mm wide
16 mm²/12 mm wide
35 mm²/16 mm wide**

Type	Part No.	Std. Pack	Type	Part No.	Std. Pack	Type	Part No.	Std. Pack		
Marking strips, unmarked			Marking strips, unmarked			10 mm²/10 mm wide				
9705 A/5/10	04.242.5053.0	25	9705 A/6/10	04.242.6053.0	25	marked for 5 blocks (every 2nd tag) *				
Marking strips, marked			Marking strips, marked			16 mm²/12 mm wide				
9705 A/5/9 B	1 - 9	04.842.4953.0	25	9705 A/6/9 B	1 - 9	04.842.5953.0	25	9705 A/5/10/5 B	04.842.5553.0	25
9705 A/5/10 B*		04.842.5053.0	25	9705 A/6/10 B*		04.842.6053.0	25	marked for 5 blocks (every 2nd tag) *		
9705 A/5/10 B	1 - 10	04.845.0153.0	25	9705 A/6/10 B	1 - 10	04.846.0153.0	25	35 mm²/16 mm wide		
	11 - 20	04.845.0253.0	25		11 - 20	04.846.0253.0	25	marked for 5 blocks (every 2nd tag) *		
	21 - 30	04.845.0353.0	25		21 - 30	04.846.0353.0	25	9705 A/6/10/5 B		
	31 - 40	04.845.0453.0	25		31 - 40	04.846.0453.0	25	04.842.6553.0		
	41 - 50	04.845.0553.0	25		41 - 50	04.846.0553.0	25	25		
	51 - 60	04.845.0653.0	25		51 - 60	04.846.0653.0	25			
	61 - 70	04.845.0753.0	25		61 - 70	04.846.0753.0	25			
	71 - 80	04.845.0853.0	25		71 - 80	04.846.0853.0	25			
	81 - 90	04.845.0953.0	25		81 - 90	04.846.0953.0	25			
	91 - 100	04.845.1053.0	25		91 - 100	04.846.1053.0	25			
	⊕ (10 x)	04.855.0053.0	25		⊕ (10 x)	04.856.0053.0	25			
	⊖ (10 x)	04.855.0153.0	25		⊖ (10 x)	04.856.0153.0	25			
	+ (10 x)	04.855.0253.0	25		+ (10 x)	04.856.0253.0	25	marked for 5 blocks (every 2nd tag) *		
	- (10 x)	04.855.0353.0	25		- (10 x)	04.856.0353.0	25	9705 A/8/10/5 B		
	L1 (10 x)	04.855.0453.0	25		L1 (10 x)	04.856.0453.0	25	04.842.8553.0		
	L2 (10 x)	04.855.0553.0	25		L2 (10 x)	04.856.0553.0	25	25		
	L3 (10 x)	04.855.0653.0	25		L3 (10 x)	04.856.0653.0	25			
	PE (10 x)	04.855.0753.0	25		PE (10 x)	04.856.0753.0	25			
	SL (10 x)	04.855.3153.0	25		SL (10 x)	04.856.3153.0	25			
	N (10 x)	04.855.3253.0	25		N (10 x)	04.856.3253.0	25			
	F1 (10 x)	04.855.0953.0	25		F1 (10 x)	04.856.0953.0	25			
	F2 (10 x)	04.855.1053.0	25		F2 (10 x)	04.856.1053.0	25			
	L1, L2, L3, N, PE (2 x)	04.855.0853.0	25		L1, L2, L3, N, PE (2 x)	04.856.0853.0	25			
with enlarged marking area			with enlarged marking area							
9705 AL/5/10	04.242.5153.0	25	9705 AL/6/10	04.242.6353.0	25					
* Custom marking upon request			* Custom marking upon request			* Specify required marking with part no.				