
4" Miniature Non-IC Housing


Catalog Number:	
Project Name:	Type:
Note:	elite

LAMP WATTAGE: (1) MAXIMUM 50W R/PAR20/A19



DESIGNED FOR 2" X 6" JOIST CONSTRUCTION














DESCRIPTION

Small aperture thermally protected, specification grade recessed housing. For new construction non-insulated ceilings or where insulation can be kept 3" from housing. Accommodates up to 50W PAR20, R20, and A19 lamps. Furnished with preinstalled adjustable bar hangers. Junction box is provided with four ½" KOs, one ¾" KO and four Romex knockouts with strain relief.

SPECIFICATION

- A. HOUSING High temperature painted 22 gauge deep drawn single piece housing. Adjusts vertically in plaster frame to accommodate 1/2" to 1-3/8" ceiling. Accommodate lamps up to 50W depending on trim used.
- B. SOCKET Medium base screw shell porcelain socket preinstalled on adjustable mounting bracket is designed to allow usage of different lamp types, as well as proper and consistent lamp positioning.
- C. BAR HANGERS Preinstalled bar hangers allow housing to be positioned and locked at any point within a 24" joist span and can be shortened for 12" joists. They contain a double-headed real nail for secure attachment into the joist. Bar hanger nails are installed on a 20° downward angle for better contact, and the 90° pivoting mounting plate makes installation fast and accurate. Bar hangers can fit onto T-Bar spline with additional slots and holes for special mounting methods if necessary.
- D. JUNCTION BOX UL and ETL listed for throughbranch circuit wiring and has four ½" KOs. one ¾" KO and four Romex knockouts with true pry-out slots and strain clamps.
- E. THERMAL PROTECTION Standard thermal protection device quards against improper installation. overlamping and misuse of insulation material.



BEAM DIA. MEASURED AT 50% OF NADIR F.C.

FEATURES

- Thermally Protected Non-IC housing.
- · Designed for accent and task lighting applications.
- · Adjustable socket bracket.
- Wire through junction box.
- · Preinstalled adjustable bar hanger.
- · Dependable, favorable design and effortless installation.
- 5 1/2" height allows use in 2" x 6" joist construction.
- Special screw on the frame locks bar hangers in place which prevents the housing from any movement once installed.
- Preinstalled socket cap provides electrical contact protection against dust, paint and over spray.

OPTIONS

AIR-SHUT

- · Gasket to prevent air flow from heated or air conditioned spaces.
- . Meets all national air flow requirements.

UL AND C-UL/ETL AND C-ETL LISTED

- For Damp location
- For Feed-through wiring

ITEM SELECTOR: (Please check the boxes below for the option desired)

ТҮРЕ	AIR-SHUT	OPTION	TRIM TYPE			BAFFLE	REFLECTOR	TRIM/RING	GL/	ASS
B4	□ AT	☐ (W) With quick connects	□ B401	□ B406	AF402	□ W	□ CL	□ WH		Green
			□ B421	□ B407	B471	□ P	□ RG	□ BK		Yellow
			□ B402	□ B462	B472	□ SN	□ W	□ SN		Pink
			□ B432	□ B452	B473	□ CP	□ МВ	□ CP		Brown
			□ B420	□ B455	B474	□ BZ	□ BZ	□ CH		Navy Blue
			□ B496	□ B451	B441		□ CP	□ PB		Orange
			□ B497	□ B454	B443		□ SN	□ BZ		Blue
			□ B403	□ B437	B442		□ SHZ			White
			□ B461	□ B438	B444					Red
			□ B405	□ B439						
			□ B422	☐ AF401						

Specifications:

B4

BAFFLE

REFLECTOR

TRIM/RING

GLASS

BAFFLE W W P Bla Black Gold W MB BZ CP Black Bronze Copper Copper

REFLECTOR

WH BK SN CP CH PB BZ Satin Nickel Copper Chrome Polish Brass

TRIM/RING

*For custom baffle, reflector, trim ring, glass color and lens options, please consult factory

CP BZ



Sample of Catalog Number: B4-AT-W-B401-W-WH



RING/TRIM FINISH:

Rlack

Copper

Satin Nickel

Chrome

Bronze

Polish Brass

PR

ΒZ

WWW.IUSEELITE.COM • TEL: 1-877-375-5555 • FAX: 1-877-375-3333

WH White

RK

SN

CP



REFLECTOR FINISH:

Chrome

White

Black

CP

SN

SHZ

Copper

Satin Nickel

Satin Haze

RG Gold

W

MB

BAFFLE FINISH:

White

Rlack

Copper

Satin Nickel

W

SN

CP

Sloped Ceiling Lighting

General

Wall Wash

Task Lighting



Exotic Glass Collection

Elite Lighting now offers a new line of exotic glass trims. The new series of glass trims can elegantly complement any color scheme in any environment. We are certain that with such a wide selection, you will find the perfect colored trim for your project.









AVAILABLE EXOTIC GLASS COLORS: GREEN, YELLOW, PINK, BROWN, NAVY BLUE, ORANGE, BLUE, WHITE, RED

PATENT #: D570,531



BAFFLE FINISH: REFLECTOR FINISH: RING/TRIM FINISH: GUIDE HOUSING COMPATIBILITY MAX. LAMP WATTAGE White Chrome Bronze WH White CH Chrome B4IC-AT-W, B4-AT-W, B4R-AT-W 50W R/PAR20 Rlack RG Gold Copper RK Rlack PR Polish Brass SN SN Satin Nickel W SN Satin Nickel Satin Nickel ΒZ White Bronze B4IC-AT-W, B4-AT-W, B4R-AT-W 35W R/PAR20 CP CP MB SHZ Black Satin Haze Copper Copper

Bronze

PB, BZ

B441WH

PB, BZ

HOUSING COMPATIBILITY GUIDE:





FLANGE


HOUSING COMPATIBILITY GUIDE:



CL, RG, W, MB, CP


WH- WHITE SELF FLANGE

HOUSING COMPATIBILITY



GUIDE HOUSING COMPATIBILITY MAX. LAMP WATTAGE B4IC-AT-W, B4-AT-W, B4R-AT-W 50W R/PAR20 B4IC-AT-W, B4-AT-W, B4R-AT-W 35W R/PAR20 EZ4IC, EZ4, EZ4R 50W R/PAR20











B474CL-WH

Square Reflector w/ Socket Bracket





B444CL-WH



B443WH











BAFFLE FINISH:					
W	White				
P	Black				
SN	Satin Nickel				
CP	Copper				
BZ	Bronze				

REFLE	CTOR FINISH:
CL	Chrome
RG	Gold
W	M/hito

MB Black

BZ	Bronze
CP	Copper
SN	Satin Nickel
SHZ	Satin Haze

RING	/TRIM FINISH:
WH	White
BK	Black
SN	Satin Nickel
CP	Copper



PATENT #: D510,151

HOUSING COMPATIBILITY GUIDE:

B442WH







Sloped Ceiling Lighting



