

# **B36IC** 6" Slope IC Housing

### LAMP WATTAGE: (1) MAXIMUM 75W R/PAR30, 60W A19, 65W BR30





#### **DESIGNED FOR 2" X 8" JOIST CONSTRUCTION**










#### DESCRIPTION

New construction, thermally protected, IC rated specification grade recessed housing. Designed for sloped ceiling applications where the ceiling pitch ranges from 2/12 to 6/12. Accommodates up to 75W PAR30, R30 lamps, 60W A19 lamps and 65W BR30 lamps. Furnished with preinstalled adjustable bar hangers. Junction box is provided with four ½" KOs, one ¾" KO and four Romex knockouts with strain relief.

#### **SPECIFICATION**

A. HOUSING - Die-formed all aluminum construction for maximum heat dissipation and rust protection. Adjusts vertically in plaster frame to accommodate 1/2" to 1-3/8" ceilings.

- B. SOCKET Medium base screw shell porcelain socket preinstalled on a mounting bracket is specially designed to swivel and rotate so the lamp could be aligned properly. The lamp will aim straight down regardless of the ceiling pitch.
- C. BAR HANGERS Preinstalled bar hangers allow housing to be positioned and locked at any point within a 24" joist span and can be shortened for 12" joists. Integral bar hanger nailers are designed to be hammered directly into the joist without additional nails or screws and makes installation fast and accurate. Bar hangers can fit onto T-Bar spline with additional slots and holes for special mounting methods if necessary.
- D. JUNCTION BOX ETL listed for through-branch circuit wiring and has four 1/2" KOs, one 3/4" KO and four Romex knockouts with true pry-out slots and strain clamps.
- E. THERMAL PROTECTION Standard thermal protection device quards against improper installation, overlamping and misuse of insulation material.



BEAM DIA. MEASURED AT 50% OF NADIR F.C.

#### **FEATURES**

- Thermally Protected IC housing.
- . The socket bracket is specially designed to swivel and rotate so the lamp could be aligned properly. The lamp will aim straight down regardless of the ceiling pitch.
- Adjustable socket bracket with a slope indicator provides consistent lamp alignment and setup.
- Wire through junction box.
- · Preinstalled adjustable bar hanger.
- Dependable, favorable design and effortless installation.
- 7-1/2" height allows use in 2" x 8" joist construction.
- Preinstalled socket cap provides electrical contact protection against dust, paint and over spray.

#### **OPTIONS AIR-SHUT**

- · Gasket to prevent air flow from heated or air conditioned spaces.
- . Meets all national air flow requirements.

#### **ETL AND C-ETL LISTED**

- For Damp location
- For Feed-through wiring
- For Direct contact with insulation


ТҮРЕ	AIR-SHUT	TRIM TYPE	BAFFLE	REFLECTOR	TRIM/RING
B36IC	□ AT	□ B391	□ W	□ CL	□ WH
		□ B392	□ P	□ RG	□ BK
		□ B602	□ SN	□ W	□ SN
		□ B646	□ CP	□ MB	□ CP
		□ B663	□ BZ	□ BZ	□ CH
		□ B673		□ CP	□ PB
		□ B601		□ SN	□ BZ
		□ B601L		□ SHZ	
		□ B605			
		☐ B605L			

_					
- 4	nΔ	CITI	ובחו	חול	ns:
•	UU	GHI	ıva	uv	mo.

**B36IC** BAFFLE REFLECTOR

\*For custom baffle, reflector, trim ring, glass color and lens options, please consult factory,





Submittal form is available @ www.iuseelite.com Tel: 323-888-1973 • Fax: 323-888-1977



# 6" Slope Ceiling **Incandescent Trims**

( LAMP WATTAGE: (1) MAXIMUM 75W R/PAR30, 60W A19, 65W BR30)


Catalog Number:	
Project Name:	Туре:
Note:	elite

## B391CP-CP **METAL STEPPED BAFFLE R30/PAR30**



BAFFLE FINISH: W, P, SN, CP, BZ

TRIM/RING FINISH: WH, BK, SN, CP, CH, PB. B7




#### **B394P-WH** PAR38/R40 STEPPED BAFFLE



**BAFFLE FINISH:** W, P, SN, CP, BZ

TRIM/RING FINISH: WH, BK, SN, CP, CH,



#### B392RG-WH R30/PAR30 REFLECTOR



REFLECTOR FINISH: CL, RG, W, MB, CP, SN. BZ

TRIM/RING FINISH: WH, BK, SN, CP, CH, PB, BZ



#### B395CP-WH R38/PAR40 REFLECTOR



REFLECTOR FINISH: CL, RG, W, MB, CP,

TRIM/RING FINISH: WH, BK, SN, CP, CH, PB. BZ



#### B601CP **METAL ALBALITE LENS**



TRIM/RING FINISH: WH, BK, SN, CP, CH, PB, BZ



### B601L

PLASTIC ALBALITE LENS



LENS: ALBALITE

TRIM/RING FINISH:



# B605PB





LENS:

TRIM/RING FINISH: WH, BK, SN, CP, CH,




TRIM/RING FINISH:



LENS:

B605L


**PLASTIC FRESNEL LENS** 



#### B663PB **PAR30 GIMBAL RING**



TRIM/RING FINISH: WH, BK, SN, CP, CH, PB, BZ




## B673P-0V

PAR30 BAFFLE W/ GIMBAL RING



**BAFFLE FINISH:** W, P, SN, CP

TRIM/RING FINISH:



## **BAFFLE** White

Black Satin Nickel Copper ΒZ Bronze

## REFLECTOR **CL** Chrome

RG Gold White MB Black CP

## Copper SN Satin Nickel

BK Black Satin Nickel CP Copper CH Chrome PB Polish Brass

> BZ Bronze

TRIM RING

WH White

\*For custom baffle, reflector, trim ring, glass color and lens options, please consult factory.