

Catalog Number
Notes
Type

FEATURES & SPECIFICATIONS

INTENDED USE

Provides accent illumination in residential and light commercial applications. Ideal for use as toe-kick lighting for counter cabinets, providing a warm inviting atmosphere in the kitchen. Also use in bookcases and display cabinets.

ATTRIBUTES

Long-lasting LEDs - 40,000 hours average bulb life. 1/2" low-profile light sticks, available in 6", 12" and 18" lengths. Quick-connect brackets or double-sided tape allows for quick and easy installation. Light sticks can be linked end-to-end for continuous illumination. 3" linking cord accessory links fixtures around corners, or for wider spacing use 24" linking cord accessory (order separately - see Accessories).

Includes 0.1-watt 3,500K LED bulbs, for a bright illumination and long life. Total wattage 0.45W 6"stick, 0.9W 12"stick and 1.35W for 18" stick.

Requires 24V step-down transformer kit (sold separately - see accessories below). Links up to 10' of fixtures on one transformer. Kit includes 6' power cord and 24" transformer linking cord. Can be direct-wired with splice box and 24" connector cord, (order separately - see Accessories below).

26" cord with in-line power switch available (order separately - see Accessories below).

All mounting hardware included.

LISTING

CUL listed to US and Canadian safety standards and suitable for damp locations.


WARRANTY

2-year limited warranty. Complete warranty terms located at www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx

Note: Specifications subject to change without notice.

Indoor General Purpose


Cabinet Light Linkable Stick - LED



DIMENSIONS

Nominal size	Model number	Number of lamps	(A) Width inches (cm)	(B) Length inches (cm)	(C) Extension* inches (cm)
6"	STK6	0.45W 24V LED	1/2" (1.3)	6-1/4" (10.5)	3/8" (1.0)
12"	STK12	0.9W 24V LED	1/2" (1.3)	12-1/4" (31.1)	3/8" (1.0)
18"	STK18	1.35W 24V LED	1/2" (1.3)	18-1/4" (46.4)	3/8" (1.0)

*Extension from ceiling
All dimensions are shown in inches (centimeters) unless otherwise noted.



ORDERING INFORMATION

For shortest lead times, configure products using **bolded options**.

Example: STK6

Series ¹	
STK6	6" - 0.45W 24-volt (6) integral LED bulbs included
STK12	12" - 0.9W 24-volt (12) integral LED bulbs included
STK18	18" - 1.35W 24-volt (18) integral LED bulbs included
STKTRANS24	24-volt transformer required ²

Accessories / Replacement parts	
INLS26	In-line power switch with 26" cord
UCD JB	Splice box (for easy direct wiring - 24" cord connector required)
UC ERC24	24" cord connector (required when using splice box)
UCH WWC	18" cord cover (conceal cords)
STKCC24	24" LED connector cord (for longer spacing between fixtures)
STKCC3	3" LED connector cord (for linking fixtures around corners)

Notes:

- Includes 0.45W 24-volt LED ballasts, 0.9W 24-volt LED ballasts or 1.35W 24-volt LED ballasts.
- Links up to 10' of fixtures per transformer. Includes 6' power cord and 24" transformer linking cord.

PHOTOMETRICS

Full photometric data report available within 2 weeks from request. Consult factory.