Project:	Туре:	QTY:
Product Code:		

for material and spec modification without prior notice. Right reserved

# **Product Code**

IP51 - 304600 -**COLOR** PCB INTENSITY **VOLTAGE 120**=120V WW27 =1180 lm

**W\***=White CC =Custom Color

**WW30\***=1200 lm WW35 =1240 lm NW40 =1280 lm

BW50 =1310 lm

Note: \* Components usually in stock for quick assembly and shipping



# **Features + Specifications**

#### Intended Use:


- Building interior, protected exterior
- 7" diameter body mounts over ceiling box
- Great for closets, utility rooms & stairwells


#### **Construction:**

- Die cast aluminum one piece base
- Power coat painted low gloss white
- Full size PMMA injection molded low profile lens
- Lens twist lock onto base for tight fit

### **Optical System:**

- Good quality multiple 2835SMDs PCB design, 10W
- WW30\*=3000K CCT, 1200 lumens minimum with 80+CRI
- 100+ lumens per watt, L70 @ 35000 hrs
- Optional CCT color WW27, WW35, NW40 & BW50 also available (These CCT might require minimum quantities with longer lead time)
- Laminated aluminum PCB for effective heat management
- PMMA frosted opal lens with 120° symmetrical light distribution





# **Electrical System:**

- HPF 90+, high efficiency constant current driver
- Short circuit + Overheat protected
- 120V AC line voltage dimmable
- RoHS compliant

## Mounting:

• Mounts directly to standard 4" outlet box

Certified to CSA C22.2 No.250.0 Conformed to UL 1598 Certification Marks (where applicable) will be found on our luminaires and its components 



















