

DURACELL®

⊕ RECHARGEABLE ACCU ⊖

ActiveCharge

Mobile Charger

CEF23

Benefits

Duracell Mobile Charger is built for convenience and portability, with a compact footprint, the ability to charge AA & AAA Batteries, and a convenient port that can charge and power other high-tech devices on the go.

Packed with Duracell Rechargeable Pre-charged Batteries - Retain power for up to 365 days while not in use, unlike regular rechargeables!

Features

USB Power Port

• Capable of charging external devices through unplugged charger with fully charged batteries

Four Independent Channel Charging Charges AA & AAA simultaneously

2-6 hour charge

Microprocessor Controlled = Always a Safe charge

Available SKU:

• 4 HR6/AA cells Included (Duracell Rechargeable Pre-charged)

Removable/Interchangeable plugs available

Car Adaptor Capability available

Safety

Microprocessor Controlled

- Charge Termination based on -dV/dt, temperature, and/or built-in timer
- Primary Cell Protection - will not charge non-rechargeable batteries
- Over-temperature shutoff - prevents overheat of cell
- Over-charge protection - prevents cell damage
- Low-voltage battery protection - prevents overheat and damage to cell
- Power Protection Circuit - resets whenever battery is removed or power is interrupted

Enclosed charging compartment provides protection

Design

Compact /"Pocket" Footprint - portability

Intuitive usage, High-tech look/feel

Consistent with consumer expectation of Duracell

International Charge Capability - device can be used world-wide (with optional interchangeable plug kit or suitable converter plug)

• Primary plug matches local requirements

Packaging with Clear Device Linkage, Leveraging Duracell Heritage



Technical

Battery Charger

Other than Class 2 Power Supply

Plug

Direct, Interchangeable Plug Matches Local Requirements

Battery Type

NiMH HR6/AA or HR03/AAA

Battery Fit

1-4 NiMH AA/HR6 or 1-4 AAA/HR03

Average Weight

171 grams (6 ounces)

Input

100-240V AC, 50-60 Hz

Output

HR6/AA: 1.5V DC 0.6A per slot
HR03/AAA: 1.5V DC 0.6A per slot

Operating Temperature

0° C - 40° C (32° F - 103° F)

Dimensions

130 mm (L) x 80 mm (W) x 30 mm (H)

*Charge rate and time is dependent on cell capacity, discharge state, and operating temperature.



Berkshire Corporate Park
Bethel, CT 06801 U.S.A.

Telephone Toll-free:
(Global) 1-203-796-4500

Internet: www.duracell.com