

DURACELL
DAYLITE
 LED FLASHLIGHT

DURACELL® DAYLITE™ FLASHLIGHT
AA

Features



- Shock-Resistant Design**
- Featuring durable, hard-anodized aircraft –grade aluminum construction
 - Survived 10-foot-drop test

- Camera Inspired Spot-to-Flood Lensing**
- No dark spots

- Patented TrueBeam Optics™ Precision-Focus Lensing**
- 80 lumens/3W LED
 - Captures up to 100% of light
 - Delivers a bright, true beam

- LED Light**
- Extends battery life with a run time of 4 hrs.

Ordering Information

Brand Code: 75061190
Case UPC: 000 41333 77148 9
Item UPC: : 000 41333 77048 2

<u>QTY</u>	<u>DESCRIPTION</u>	<u>SIZE</u>
4	DAYLITE Flashlight	2AA

Case Dimensions: 8.5" x 6.69" x 6.25"
Item Dimensions: 8.125" x 5.250" x 1.655"

Case Weight: 2.17 **Pallet Weight:** 471 lbs.
Case Cube: 0.21 **COF:** 2.88
Stat: 0.400
Cases/Layer: 31 **Layers/Pallet:** 7
Cases/Pallet: 217



0 00 41333 77148 9

Case Code



0 41333 77048 2

PKG Code

Technical

Battery	2 AA
Dimensions	diameter = 36.55mm length = 144 mm
Weight	142.4 g
Lumens	80
LED*	3 Watt

DURACELL®

Berkshire Corporate Park
 Bethel, Ct 06801 U.S.A.
 Telephone toll-free:

(North America only) 1-800-544-5454
 (Global) 1-203-796-4500
 Internet: www.duracell.com

*As rated by the manufacturer.