




MN918

Size: Lantern (4LR25-2)


Zn/MnO₂

Alkaline-Manganese Dioxide Battery




| | |
|------------------------------|---|
| Nominal Voltage: | 6 V |
| Nominal Internal Impedance: | 330 m-ohm @ 1kHz |
| Average Weight: | 1310 gm (46 oz.) |
| Volume: | 1074 cm ³ (65.5 in. ³) |
| Terminals: | Screw Caps |
| Operating Temperature Range: | -20°C to 54°C (-4°F to 130°F) |
| ANSI: | 918A |
| IEC: | 4LR25-2 |

Typical Discharge Characteristics at 21°C (70°F)



Typical Discharge Characteristics at 21°C (70°F)



DURACELL[®]
BATTERIES

Berkshire Corporate Park
Bethel, CT 06801 U.S.A.
Telephone: Toll-free 1-800-544-5454
Internet: www.duracell.com

* Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage. Please refer to the charts and discharge data shown for examples of the energy / service life that the battery will provide for various load conditions.