

# FLASHLIGHTS



## THE STICK BUG

The Pocket Light just got brighter, stronger and better. Some call it supercharged! With the new technology of COB LED technology, it has 150/160 lumens - 2 times the amount of the original pocket light. With the durable and strong pocket clip and improved magnetic base, you'll never be left out in the dark again

### FEATURES:

- COB LED
- 160 Lumens
- Operates on (3) AAA batteries
- Up to 7 hours run time
- Water resistant button

Stick Bug - 160 lumens - Part# 53600

Stick Bug Jr - 60 lumens - Part# 53500



## FIREFLY Part# 53400

The Fire Fly is a compact aluminum flashlight that features 3 light outputs with and has an output of 120 lumens.

### FEATURES:

- 120 lumen output
- Light Modes: High output, low output, flash
- Mechanical zoom function
- 3 AAA batteries included

## THE OWL EYE Part# 53300

Multi-function electronic switch. Softly press the switch once for high output. Press the switch and hold for dimming function (10%-100% brightness), press quickly two times at any position for strobe function.

**Takes 3X AAA Batteries (not included)**

### FEATURES:

- Waterproof
- Dust-proof
- 120 Lumens



## HEAD LIGHT

### USB RECHARGEABLE

Part# 54075

Bulb: COB LED

Max Output: 150 Lumens

3 Modes: High, Low and Strobe

Runtime: High (4 Hours) Low (12 Hours)

4-hour charge time

Impact and Water Resistance

### STANDARD BATTERY OPERATED

Part# 54050

Features:

Bulb: COB LED

3 AAA Batteries Included

Runtime: 5 hours

Max Output: 150 Lumens



## THE GOPHER II Part# 53020

### LED Rechargeable Flashlight

- One high powered LED bulb outputs 35 lumens of light
- Weather-resistant compact body design
- Anodized aluminum sturdy construction
- Built-in rechargeable batteries
- Charges directly from cigarette lighter socket
- 120 minutes usage, full recharge in 6-8 hours



## GLOW SAFE 360°

The Glow Safe 360 attaches to any hard hat and produces a ring of light around the wearer, enabling him or her to be easily seen in all directions.

### FEATURES:

- Shadow-free, panoramic visibility
- Non-slip hard hat attachment
- Only 40 grams (1.4 oz) extra hard hat weight
- Powered by two button cells or rechargeable LED
- Operates up to 24 hours with premium brand batteries or USB Charger



Standard: Part#54000

Rechargeable: Part#54020

## BAT LIGHT

The Bat flashlight has a durable, scratch and corrosion resistant anodized aluminum frame.

### 10" Bat Flashlight

Part# 53700

- 3W Cree LED 300 Lumens

- 3 x AA Batteries Included

### 12" Bat Flashlight

Part# 53750

- 3W Cree LED 300 Lumens

- 3 x AAA Batteries Included

