FLASHLIGHTS



THE STICK BUG

The Pocket Light just got brighter, stronger and better. Some call it supercharged! With the new technology of COB LED technology, it has 150/160 lumens - 2 times the amount of the original pocket light. With the durable and strong pocket clip and improved magnetic base, you'll never be left out in the dark again

- COB LED
- 160 Lumens
- Operates on (3) AAA batteries
- Up to 7 hours run time
- Water resistant button

Stick Bug - 160 lumens - Part# 53600 Stick Bug Jr - 60 lumens - Part# 53500



HEAD LIGHT

USB RECHARGEABLE

Part# 54075 Bulb: COB LED

Max Output: 150 Lumens 3 Modes: High, Low and Strobe

Runtime: High (4 Hours) Low (12 Hours)

4-hour charge time

Impact and Water Resistance

STANDARD BATTERY OPERATED

Part# 54050 Features:

Bulb: COB LED

3 AAA Batteries Included

Runtime: 5 hours

Max Output: 150 Lumens



The Bat flashlight has a durable, scratch and corrosion resistant anodized aluminum

10" Bat Flashlight

Part# 53700

- 3W Cree LED 300 Lumens
- 3 x AA Batteries Included

12" Bat Flashlight

Part# 53750

- 3W Cree LED 300 Lumens
- 3 x AAA Batteries Included



Part# 53400

The Fire Fly is a compact aluminum flashlight that features 3 light outputs with and has an output of 120 lumens.

FEATURES:

- 120 lumen output
- Light Modes: High output, low output, flash
- Mechanical zoom function
- 3 AAA batteries included



THE OWL EYE Part# 53300

Multi-function electronic switch. Softly press the switch once for high output. Press the switch and hold for dimming function (10%-100% brightness), press quickly two times at any position for strobe function. Takes 3X AAA Batteries (not included)

- Waterproof
- Dust-proof-
- 120 Lumens



THE GOPHER II

LED Rechargable Flashlight

- One high powered LED bulb outputs 35 lumens of light
- Weather-resistant compact body design
- Anodized aluminum sturdy construction
- Built-in rechargeable batteries
- Charges directly from cigarette lighter socket
- 120 minutes usage, full recharge in 6-8 hours

GLOW SAFE 360°

The Glow Safe 360 attaches to any hard hat and produces a ring of light around the wearer, enabling him or her to be easily seen in all directions.



- Shadow-free, panoramic visibility
- Non-slip hard hat attachment
- Only 40 grams (1.4 oz) extra hard hat weight
- Powered by two button cells or rechargable LED
- Operates up to 24 hours with premium brand batteries or USB Charger

Standard: Part#54000 Rechargable: Part#54020