



CONTINUED...

## Ordering Information

Catalogue Number	Description
FSP101G*	Conventional fire alarm control panel - 1 class B IDC and 1 class B NAC, 120VAC, english, order up to 4.5Ah battery separately, surface mount only
FSP302G*	Conventional fire alarm control panel - 3 class B IDCs and 2 class B NACs, 120VAC, english, order up to 26Ah battery separately (7.2Ah max in cabinet)
FSP502 G*	Conventional fire alarm control panel -5 class B IDCs and 2 class B NACs (pairs of IDCs & NACs convertible to single class A circuits), 120VAC, english, order up to two 26Ah battery separately (7.2Ah max in cabinet)
FSP1004G*	Conventional fire alarm control panel - 10 class B IDCs and 4 class B NACs (pairs of IDCs & NACs convertible to single class A circuits), 120VAC, english, order up to two 26Ah battery separately (18Ah max in cabinet)
F-XTR120	Expander transformer, 120VAC - increases available panel power to 7.5 amps (FSP1004GC only)
EOL-P1	End of line resistors and plate. Package includes 4.7KW, 3.6KW and 1.1KW and various other resistors. One required per circuit
F-TRIM35G	Semi-flush trim kit for 3 and 5 zone panels
F-TRIM10G	Semi-flush trim kit for 10 zone panel

\*For French change "G" to "F"

### Off Premises Communications

F-DACT	Digital Communicator/Modem/LCD module (Mounts in 3, 5 or 10 zone control panel) For French order F-DACTF
CTM	City Tie Module (Requires 4" square or 2-gang North American electrical box)
RPM	Reverse Polarity Module (Requires MFC-A or other listed fire alarm enclosure)

### Remote Annunciation

FSRSI	Remote System Indicator – Includes LEDs for display of Power, Alarm, Supervisory, Trouble and Ground Fault, trouble sounder and silence/lamp test switch. Single gang trim plate included, multi-gang plates ordered separately. Mounts in a single or multi-gang North American electrical box.
FSRZI-A	Remote Zone Indicator – Includes red LEDs for five IDCs. Single gang trim plate included, multi-gang plates ordered separately. Mounts in single or multi-gang North American electrical box.
FSRZI-SA	Remote Zone Indicator – Includes LEDs for five IDCs. Single gang trim plate included, multi-gang plates ordered separately. Mounts in single or multi-gang North American electrical box. Jumper selected Alarm (red) or Supervisory (amber) indications.
FSAT1	Annunciator Trim Plate, 1 gang
FSAT2	Annunciator Trim Plate, 2 gang
FSAT3	Annunciator Trim Plate, 3 gang
FSAT4	Annunciator Trim Plate, 4 gang
FSRA10	Single Unit 10 zone remote annunciator – Insert "F" after p/n for French language option
FSRA10C	Single Unit 10 zone remote annunciator (with common controls) – Insert "F" after p/n for French language option
FSUIM	Common Function Graphic Driver/Interface - 9 relays and 5 switch inputs for common system indicators and controls. Contact your local Chubb Edwards sales representatives for more detailed ordering information and application.
LSRA-SB	Surface Box for FSRA10 Series annunciators
STI-7500H	Clear protective cover to protect common controls on FSRA10C Series annunciators
RTU(**)	Remote Trouble Unit, single gang, English.

### Remote Relay Module

FSRRM24	Remote Relay Module – Five Form C relays. Configurable for IDCs 1-5, or 6-10, or common system indications. Requires MFC-A or other listed fire alarm enclosure.
FSRRM-S11	11" Mounting track. Holds up to 4 FSRRM24s.

### Batteries & Boxes

12V4A5	12V, 4.5Ah (two required), 4.2"H x 2.8"W x 3.5" L per cell
12V7A2	12V, 7.2Ah (two required), 3.7"H x 2.6"W x 5.9" L per cell
12V18A	12V, 18Ah (two required), 6.5"H x 3.0"W x 7.1" L per cell
12V26A	12V, 26Ah (two required) 6.6"H x 4.9"W x 6.9"L per cell. Requires BC-1 Battery Cabinet.
BC-1	Battery Cabinet, supports two 12V26A batteries (14"H x 18.25"W x 7.25"D)
BC-2	Battery Cabinet, supports up to 18Ah standby batteries (15"H x 22"W x 3.75"D)
MFC-A	Multi-function enclosure, listed for fire use (8"H x 14"W x 3.5"D)

\*\* Add C for Bilingual