VISUAL SIGNALS



FEATURES

- > Weatherproof
- > Light intensifying reflector
- > 75 revolutions per minute
- Bayonet lamp socket for easy replacement
- Cast base can be utilized as junction box
- > May be mounted vertically, facing up or down in 3 ways:
 - Direct Surface
 - 4" (102mm) octagon box
 - 1/2" (13mm) NPT conduit

AGENCY APPROVALS

- > UL 1638 Listed
- > cUL Listed

AdaptaBeacon® Rotating Lights

Weatherproof

52 Series

Rotating signal designed to provide maximum brilliance and long term durability with minimum maintenance. The polycarbonate dome allows for easy cleaning. May be mounted in any orientation.

For direct mounting applications, unit is supplied complete with gasket and rubber expansion plugs. For weatherproof installation unit must be mounted vertically with the dome facing up. May be corner mounted using the Cat. No. CBR, corner mount bracket, or wall mounted using the Cat. No. WBR, wall mount bracket. See AdaptaBeacon Accessories, page 3-118.

Designed to attract attention or indicate equipment malfunctions in noisy areas. Used in security systems to visually show indication of an intrusion. Also used in factory and distribution facilities to alert workers of oncoming fork truck traffic.

D-04

3-20


90 Fieldstone Court | Cheshire, CT 06410 Ph: 203.699.3300 | Fx: 203.699.3108 www.edwards-signals.com



© Copyright 2004 Edwards



TECHNICAL INFORMATION



Cat. No.	Lens Color	Replacement Lens Cat. No.	Lamp Ratings	Revolution Rate	Electrical Ratings	Replacement Lamp Cat. No.
52C-N5-40WH 52R-N5-40WH 52A-N5-40WH 52B-N5-40WH 52G-N5-40WH 52M-N5-40WH	Clear Red Amber Blue Green Magenta	52-LC 52-LR 52-LA 52-LB 52-LG 52-LM	40 Watts 265 lumens* 3328 candlepower 25,000 hours**	75 rpm	120V 50/60 Hz 0.35 Amps	50-LMP-40WH
52C-G5-20WH 52R-G5-20WH 52A-G5-20WH 52B-G5-20WH 52G-G5-20WH 52M-G5-20WH	Clear Red Amber Blue Green Magenta	52-LC 52-LR 52-LA 52-LB 52-LG 52-LM	20 Watts 226 lumens* 2839 candlepower 25,000 hours**	75 rpm	24V 50/60 Hz 0.8 Amps	50-LMP-20WH
52C-R5 52R-R5 52A-R5 52B-R5 52G-R5 52M-R5	Clear Red Amber Blue Green Magenta	52-LC 52-LR 52-LA 52-LB 52-LG 52-LM	25 Watts 232 lumens* 2914 candlepower 120 hours**	75 rpm	240V 50/60 Hz 0.10 Amps	P-041917-0039 Industry Trade No. 25T8/240V/DC/CL

*Manufacturer's lumen rating. **Projected lamp life based on manufacturer's calculated lamp life @ 65 FPM and 50% duty cycle.

© Copyright 2004 Edwards



3-21

D-04