


for P1000 & P2000 Channels - With Spring

Part No.	Size	Mass kg/100
P1006	M6	3.18
P1007	M8	3.18
P1008	M10	4.54
P1010	M12	5.45
P1012S	M16	9.53

Without Spring


Part No.	Size	Mass kg/100
P3016	M6	1.00
P3006	M6	2.72
P3007	M8	2.72
P3008	M10	4.41
P3010	M12	3.64
P1012	M16	9.08




P1006/7/8/10



P3006/7/8/10



P1012S



P3016



P1012

P3300 & P4000 Channels - With Spring

Part No.	Size	Mass kg/100
P4006	M6	2.73
P4007	M8	2.73
P4008	M10	4.42
P4010	M12	3.65
P4012S	M16	4.99

Without Spring


Part No.	Size	Mass kg/100
P3016	M6	1.00
P3006	M6	2.72
P3007	M8	2.72
P3008	M10	4.41
P3013	M12	4.20
P4012	M16	4.54




P4006/7/8/10




P3006/7/8/10/13



P4012S



P3016



P4012

P5500 Channels - With Spring


Part No.	Size	Mass kg/100
P5508	M10	4.54
P5510	M12	5.45

Without Spring

Part No.	Size	Mass kg/100
P3016	M6	1.00
P3006	M6	2.72
P3007	M8	2.72
P3008	M10	4.41
P3010	M12	3.64
P1012	M16	9.08



P5508/10



P3016



P3006/7/8/10



P1012