

Table Top Rack Cabinet *RCBS Series*

Features



- Constructed in 16-gauge steel.
- Choice of three depths:
 - 13" (330 mm)
 - 17.5" (444 mm)
 - 24.5" (622 mm).
- Two pairs of fixed 19" EIA-310-D compliant round hole punched rails.
- Includes rubber feet, two lifting handles, a starter pack of 10-32 clip nuts & matching quantity of 1421ABK black screws.
- Available in finished in textured black or Light Gray (RAL7035) powder paint.
- Tested to nearly double the suggested load rating of 600 lbs.
- RoHS Compliant.
- Manufactured in North America.

Accessories

[Outlet Strips](#)

- [Rack Panels](#)



Part No.	Part No.	Overall Dimensions			Usable Mounting Dimensions			Number of Clip Nuts	S
					Height	Depth	Units		
Black	Light Gray	Height	Width	Depth	Height	Depth	Rack Units	Included	
RCBS1900313BK1	RCBS1900313LG1	5.50	21.00	13.00	3.50	12.38	2U	8	
RCBS1900513BK1	RCBS1900513LG1	7.25	21.00	13.00	5.25	12.38	3U	8	
RCBS1900713BK1	RCBS1900713LG1	9.00	21.00	13.00	7.00	12.38	4U	8	
RCBS1900813BK1	RCBS1900813LG1	10.75	21.00	13.00	8.75	12.38	5U	16	
RCBS1901013BK1	RCBS1901013LG1	12.50	21.00	13.00	10.50	12.38	6U	16	
RCBS1901213BK1	RCBS1901213LG1	14.25	21.00	13.00	12.25	12.38	7U	16	
RCBS1901413BK1	RCBS1901413LG1	16.00	21.00	13.00	14.00	12.38	8U	16	
RCBS1900317BK1	RCBS1900317LG1	5.50	21.00	17.50	3.50	16.88	2U	8	
RCBS1900517BK1	RCBS1900517LG1	7.25	21.00	17.50	5.25	16.88	3U	8	
RCBS1900717BK1	RCBS1900717LG1	9.00	21.00	17.50	7.00	16.88	4U	8	
RCBS1900817BK1	RCBS1900817LG1	10.75	21.00	17.50	8.75	16.88	5U	16	
RCBS1901017BK1	RCBS1901017LG1	12.50	21.00	17.50	10.50	16.88	6U	16	
RCBS1901217BK1	RCBS1901217LG1	14.25	21.00	17.50	12.25	16.88	7U	16	
RCBS1901417BK1	RCBS1901417LG1	16.00	21.00	17.50	14.00	16.88	8U	16	
RCBS1900324BK1	RCBS1900324LG1	5.50	21.00	24.50	3.50	23.88	2U	8	
RCBS1900524BK1	RCBS1900524LG1	7.25	21.00	24.50	5.25	23.88	3U	8	
RCBS1900724BK1	RCBS1900724LG1	9.00	21.00	24.50	7.00	23.88	4U	8	
RCBS1900824BK1	RCBS1900824LG1	10.75	21.00	24.50	8.75	23.88	5U	16	
RCBS1901024BK1	RCBS1901024LG1	12.50	21.00	24.50	10.50	23.88	6U	16	
RCBS1901224BK1	RCBS1901224LG1	14.25	21.00	24.50	12.25	23.88	7U	16	
RCBS1901424BK1	RCBS1901424LG1	16.00	21.00	24.50	14.00	23.88	8U	16	



Data subject to change without notice.

© 2013. Hammond Manufacturing Ltd. All rights reserved.