

Four Post Mounting Storage Drawer *RDRW Series*

Features



- Standard 19" rack mount.
- Plastic front pull handle.
- Inside of drawer width is 16.375" wide.
- Complete drawer with slides, hardware, lock & two keys.
- Drawer shroud, 14 Gauge steel construction.
- Available in 3 depths.
- Rear support brackets included for all depths or can be supported from rear accessory rail.
- Drawer interior smooth white powder paint for high visibility.
- Front face finished in tough textured powder paint.
- RDRW1900322BK1 tested to nearly double the suggested load rating of 60 pounds (no rear support)
- RDRW2400822BK1 tested to nearly double the suggested load rating of 120 pounds (with rear support)
- RoHS Compliant.
- Manufactured in North America.

Accessories

Mounting Hardware

Part No. Black	Part No. Beige	Part No. Light Gray	Rack Units	Drawer Height	Slide Travel
RDRW1900312BK1	RDRW1900312CG1	RDRW1900312LG1	2U	3.50	12.00
RDRW1900512BK1	RDRW1900512CG1	RDRW1900512LG1	3U	5.25	12.00
RDRW1900712BK1	RDRW1900712CG1	RDRW1900712LG1	4U	7.00	12.00
RDRW1900812BK1	RDRW1900812CG1	RDRW1900812LG1	5U	8.75	12.00
RDRW1901212BK1	RDRW1901212CG1	RDRW1901212LG1	7U	12.25	12.00
RDRW1900316BK1	RDRW1900316CG1	RDRW1900316LG1	2U	3.50	16.00
RDRW1900516BK1	RDRW1900516CG1	RDRW1900516LG1	3U	5.25	16.00
RDRW1900716BK1	RDRW1900716CG1	RDRW1900716LG1	4U	7.00	16.00
RDRW1900816BK1	RDRW1900816CG1	RDRW1900816LG1	5U	8.75	16.00
RDRW1901216BK1	RDRW1901216CG1	RDRW1901216LG1	7U	12.25	16.00
RDRW1900322BK1	RDRW1900322CG1	RDRW1900322LG1	2U	3.50	22.00
RDRW1900522BK1	RDRW1900522CG1	RDRW1900522LG1	3U	5.25	22.00
RDRW1900722BK1	RDRW1900722CG1	RDRW1900722LG1	4U	7.00	22.00
RDRW1900822BK1	RDRW1900822CG1	RDRW1900822LG1	5U	8.75	22.00
RDRW1901222BK1	RDRW1901222CG1	RDRW1901222LG1	7U	12.25	22.00

*Note: "CG1" (Beige color) is being phased out from stock - replaced with "LG1" a light gray (RAL7035)

