

# HALOGEN LAMPS

## Single-Ended Linear, Double-Ended Linear, Capsule Lamps

Watts	Bulb	Base	Product Number	Symbols, Footnotes	Ordering Code	Volts	Pkg. Qty.‡	Description	Class, Filament	MOL (In.)	Rated Avg. Life (Hrs.)(93)	Approx. MBCP*	Lumens
-------	------	------	----------------	--------------------	---------------	-------	------------	-------------	-----------------	-----------	----------------------------	---------------	--------

### HALOGEN SINGLE-ENDED LINEAR LAMPS BLISTER-CARDED (95)

50	T4	Mini-Can	20347-1		BC50Q/CL	120	12	Blister Card	C, CC-8	2¼	1000	—	500
75	T4	Mini-Can	20359-6		BC75Q/CL	120	12	Blister Card	C, CC-8	3	1000	—	1050
100	T4	Mini-Can	20350-5		BC100Q/CL ESN	120	12	Blister Card	C, CC-8	2½	1000	—	1600
150	T4	Mini-Can	20354-7		BC150Q/CL ETG	120	12	Blister Card	C, CC-8	3	1000	—	2800

### HALOGEN SINGLE-ENDED LINEAR LAMPS (95)

100	T4	D.C. Bay	44278-0		100Q/CL/DC ESR	120	12	Clear	C, CC-8	2½	1000	—	1600
150	T4	Mini-Can	29856-2		150Q ETH	120	12	Frost	C, CC-8	3	1000	—	2700
			20049-3		150Q/CL	130	12	Clear	C, CC-8	3	1000	—	2800
	T4	D.C. Bay	26676-7		150Q/CL/DC ETC	120	12	Clear	C, CC-8	2½	1000	—	2800
250	T4	Mini-Can	14668-8		250Q/CL EHT	120	12	Clear	C, CC-8	3½	1000	—	5000
			14667-0		250Q/CL	130	12	Clear	C, CC-8	3½	1000	—	5000
	T4	D.C. Bay	14666-2		250Q/CL/DC ESS	120	12	Clear	C, CC-8	3	1000	—	5000
			14669-6		250Q/CL/DC	130	12	Clear	C, CC-8	3	1000	—	5000
500	T4	Mini-Can	38079-0		500Q/CL EVR	120	12	Clear	C, C-8	3½	2000	—	10,000
750	T5	Med. 2-Pin	26972-0		750Q/CL EHG	120	24	Clear	C, CC-8	4¼	2000	—	15,000

### HALOGEN DOUBLE-ENDED LINEAR LAMP BLISTER-CARDED (99)

100	T3	RSC	20352-1		BC100T3Q/CL	120	12	Blister Card	C, C-8	3½	2000	—	1400
150	T3	RSC	20353-9		BC150T3Q/CL	120	12	Blister Card	C, C-8	3½	2000	—	2400
			20343-0		BC150T3Q/CL LONG	120	12	Blister Card	C, C-8	4½	1500	—	2400
250	T3	RSC	20360-4		BC250T3Q/CL	120	12	Blister Card	C, C-8	3½	1500	—	4000
300	T3	RSC	20355-4		BC300T3Q/CL	120	12	Blister Card	C, C-8	4½	2000	—	5200
			20336-4		BC300T3Q/CL/TP	120	12	Blister Card	C, C-8	4½	2000	—	5200
500	T3	RSC	20356-2		BC500T3Q/CL	120	12	Blister Card	C, C-8	4½	2000	—	9500
			20341-4		BC500T3Q/CL/TP	120	12	Blister Card	C, C-8	4½	2000	—	9500

### HALOGEN DOUBLE-ENDED LINEAR LAMP (99)

300	T3	RSC	39282-9		300T3Q/CL EHM	120	12	Clear	C, C-8	4½	2000	—	5200
500	T3	RSC	13223-3		500T3Q/CL	125-130	12	Clear	C, C-8	4½	2000	—	9200
			20010-5		500T3Q/CL FCL	120	12	Clear	C, C-8	4½	2000	—	9500
1000	T3	RSC	15040-9		1000T3Q/CL	240	12	Clear	C, C-8	10½	2000	—	21,500
1500	T3	RSC	15039-1		1500T3Q/CL	277	12	Clear	C, C-8	10½	2000	—	33,000
			13226-6		1500T3Q/CL	240	12	Clear	C, C-8	10½	2000	—	32,250

### HALOGEN MAINS-VOLTAGE CAPSULE LAMP BLISTER-CARDED (95)

35	T4	GY8.6	20345-5		BC35W/T4/120V/CAPSULE	120	12	Blister Card	C, CC2V	1½	2500	—	400
50	T4	GY8.6	20348-9		BC50W/T4/120V/CAPSULE	120	12	Blister Card	C, C-8	2¼	2500	—	600
75	T4	GY8.6	20349-7		BC75W/T4/120V/CAPSULE	120	12	Blister Card	C, C-8	2¼	2000	—	1200
100	T4	GY8.6	20346-3		BC100W/T4/120V/CAPSULE	120	12	Blister Card	C, C-8	2¼	2500	—	1650

For the most current product information, go to the e-catalog on [www.philips.com](http://www.philips.com)

Halogen symbols and footnotes located on page 116

