

**Horizontal Baffle** ☆

High temperature phenolic horizontal baffle available in black to reduce glare or white, for a uniform look. Aluminum reflector finished in white operates effectively with A, PAR and BR lamps. Sold complete all in one box, with a pre-wired frame for a new or insulated ceiling. (See lighting data at the end of this Guide).

INCANDESCENT COMPLETE UNIT			
NON-IC	IC/AIRSEAL®		
<b>Comple Units</b> 50W PAR20 50W R20			<b>0020</b> Black Baffle <b>0020WH</b> White Baffle
	<b>Comple Units</b> 50W PAR20 50W R20		<b>0020IC</b> Black Baffle <b>0020ICWH</b> White Baffle
<b>Comple Units</b> 100W A19 85W BR30 75W PAR30			<b>0030</b> Black Baffle <b>0030WH</b> White Baffle
	<b>Comple Units</b> 75W PAR30 75W BR30 40W A19		<b>0030IC</b> Black Baffle <b>0030ICWH</b> White Baffle
<b>Comple Units</b> 150W PAR38 150W BR40 100W A19			<b>0040</b> Black Baffle <b>0040WH</b> White Baffle



**Grooved Baffle** ☆

Aluminum reflector grooved on the inside for baffle appearance. Interior painted black to reduce glare. Operates effectively with PAR and BR lamps. A lamps recommended for white version only. White version is all white for a uniform look. Sold complete, all in one box, with a pre-wired frame for a new or insulated ceiling. (See lighting data at the end of this Guide).

INCANDESCENT COMPLETE UNIT			
NON-IC	IC/AIRSEAL®		
<b>Comple Units</b> 100W A19 85W BR30 75W PAR30			<b>0035</b> Black Baffle <b>0035WH</b> White Baffle
	<b>Comple Units</b> 75W PAR30 75W BR30 60W A19		<b>0035IC</b> Black Baffle <b>0035ICWH</b> White Baffle
<b>Comple Units</b> 150W PAR38 150W BR40 100W A19			<b>0045</b> Black Baffle <b>0045WH</b> White Baffle

