

Specular Alzak® Cone ☆☆

Versatile, low brightness downlights. Specular Alzak® heavy gauge aperture cone and recessed lamp control glare. Cone can easily be removed to facilitate maintenance.



Note: For dimming options, please consult the corresponding product Spec Sheet on www.canlyte.com.

| COMPACT FLUORESCENT | | INCANDESCENT | | | | 2005CL Specular Clear Alzak® 2005BA Specular Black Alzak® 2005CCD Comfort Clear™ Diffuse |
|--|---|---|--|---|--|---|
| NON-IC | IC/AIRSEAL® | NON-IC | IC | IC/AIRSEAL® | | |
| | | 2002 50W PAR20/R20 75W PAR16 60W A19 | 2002IC 50W PAR20 50W R20 | 2004ICX-CDN 50W PAR20 50W R20 | | |
| | | REMODELER | | | | |
| | | 2003RS-CDN 50W PAR20/R20 75W PAR16 60W A19 | | | | |
| COMPACT FLUORESCENT | | INCANDESCENT | | | | 1005CL Specular Clear Alzak® 1005BA Specular Black Alzak® 1005CCD Comfort Clear™ Diffuse |
| NON-IC | IC/AIRSEAL® | NON-IC | IC | IC/AIRSEAL® | | |
| 1001F13N120 1001F13N347 1X13W QT/TTT 1001F18N120 1001F18N347 1X18W TTT | 1004ICF13N120 1004ICXF13N120 1X13W QT/TTT 1004ICF18N120 1004ICXF18N120 1X18W TTT 1004ICF26N120 1004ICXF26N120 1X26W TTT | 1002 75W PAR30* 85W BR30 100W A19 1004IC-CDN 75W PAR30* 85W BR30 60W A19 | 1002IC 75W PAR30* 75W BR30 40W A19 | 1004IC-CDN 50W PAR30 65W BR30 40W A19 1004ICX-CDN 75W PAR30* 85W BR30 60W A19 | | |
| REMODELER | REMODELER | REMODELER | | REMODELER | | |
| 1003RF18N120 1003RF18N347 1X18W TTT | 1004ICRF13N120 1X13W QT/TTT 1004ICRF18N120 1X18W TTT 1004ICRF26N120 1X26W TTT | 1003RS-CDN 75W PAR30 85W BR30 100W A19 1004ICRS-CDN 75W PAR30* 85W BR30 60W A19 | | 1004ICRS-CDN 50W PAR30 65W BR30 40W A19 | | |
| METAL HALIDE | | | | | | |
| NON-IC | | | | | | |
| 1001H20HY1 1001H20HY1-347 20W PAR30 | | 1001H39HY1 1001H39HY1-347 39W PAR30 | | 1001H70HY1 1001H70HY1-347 70W PAR30 | | |
| COMPACT FLUORESCENT | | INCANDESCENT | | | | 1105CL Specular Clear Alzak® 1105BA Specular Black Alzak® 1105CCD Comfort Clear™ Diffuse |
| NON-IC | IC/AIRSEAL® | NON-IC | IC | IC/AIRSEAL® | | |
| 1101F13N120 1101F13N347 1X13W QT/TTT 1101F18N120 1101F18N347 1X18W QT/TTT 1101F263242N120 1101F263242N347 1X26/32W TTT | 1104ICF13N120 1X13W QT/TTT 1104ICF18N120 1104ICXF18N120 1X18W QT/TTT 1104ICF26N120 1104ICXF263242N120 1X26W TTT | 1102 150W PAR38 150W BR40 150W A21 1104IC-CDN 100W PAR38 150W BR40 75W A19 | 1102IC 90W PAR38* 100W BR40 60W A19 | 1104IC-CDN 75W PAR38 65W BR40 40W A19 1104ICX-CDN 90W PAR38* 100W BR40 60W A19 | | |
| REMODELER | REMODELER | REMODELER | | REMODELER | | |
| 1103RF18N120 1103RF18N347 1X18W QT/TTT 1103RF263242N120 1103RF263242N347 1X26/32W TTT | 1104ICRF13N120 1X13W QT/TTT 1104ICRF18N120 1X18W QT/TTT 1104ICRF26N120 1X26W TTT | 1103RS-CDN 150W PAR38 150W BR40 150W A21 1104ICRS-CDN 100W PAR38 150W BR40 75W A19 | | 1104ICRS-CDN 75W PAR38 65W BR40 40W A19 | | |
| METAL HALIDE | | | | | | |
| NON-IC | | | | | | |
| 1101H70HY1 1101H70HY1-347 70W PAR38* | | | 1101H10HY1 1101H10HY1-347 100W PAR38 | | | |

*See photometry p. 550 to 552.