

Horizontal Open Downlight ☆☆☆

Horizontal lamp position hides light source and ensures glare control. Unitized Optics system provides consistently correct lamp alignment. Deep lamp position assures excellent cut-off (55 degrees). Easy front relamping.



Note: For dimming options, please consult the corresponding product Spec Sheet on www.canlyte.com.

COMPACT FLUORESCENT		INCANDESCENT				1142TCL Specular Clear Alzak® 1142TCD Comfort Clear™ Diffuse
NON-IC	IC/AIRSEAL®	NON-IC	IC	IC/AIRSEAL®		
1101T13N120 1101T13N347 2X13W QT 1101T18N120 1101T18N347 2X18W QT*						
COMPACT FLUORESCENT		INCANDESCENT				1142T26CL Specular Clear Alzak® 1142T26CD Comfort Clear™ Diffuse
NON-IC	IC/AIRSEAL®	NON-IC	IC	IC/AIRSEAL®		
1101T26N120 1101T26N347 2X26W QT*						

Deep Alzak® Reflector ☆☆☆

The best efficiency and glare control. Lamp is fully recessed in a deep, specular Alzak® reflector, precisely contoured to assure 38° shielding of lamp and lamp image. Vertically adjustable socket holder on 1100 series provides lamping flexibility.



Note: For dimming options, please consult the corresponding product Spec Sheet on www.canlyte.com.

COMPACT FLUORESCENT		INCANDESCENT				1046CL Specular Clear Alzak® 1046CCD Comfort Clear™ Diffuse
NON-IC	IC/AIRSEAL®	NON-IC	IC	IC/AIRSEAL®		
1001F13N120 1001F13N347 1X13W QT/TTT 1001F18N120 1001F18N347 1X18W TTT 1001F26N120 1001F26N347 1X26W TTT*	1004ICF13N120 1004ICXF13N120 1X13W QT/TTT 1004ICF18N120 1004ICXF18N120 1X18W TTT 1004ICF26N120 1004ICXF26N120 1X26W TTT*	1002 100W A19 85W BR30 75W PAR30L 1004IC-CDN 60W A19	1002IC 60W A19 75W BR30 75W PAR30L	1004IC-CDN 40W A19 1004ICX-CDN 60W A19		
REMODELER	REMODELER	REMODELER		REMODELER		
1003RF18N120 1003RF18N347 1X18W TTT 1003RF26N120 1003RF26N347 1X26W TTT*	1004ICRF13N120 1X13W QT/TTT 1004ICRF18N1201 1X18W TTT	1003RS-CDN 100W A19 85W BR30 75W PAR30L 1004ICRS-CDN 60W A19		1004ICRS-CDN 40W A19		
COMPACT FLUORESCENT		INCANDESCENT				1146CL Specular Clear Alzak® 1146CCD Comfort Clear™ Diffuse
NON-IC	IC/AIRSEAL®	NON-IC	IC	IC/AIRSEAL®		
1101F13N120 1101F13N347 1X13W QT/TTT 1101F18N120 1101F18N347 1X18W QT/TTT 1101F263242N120 1101F263242N347 1X26W TTT 1X32*/42W TTT	1104ICXF18N120 1X18W QT/TTT 1104ICXF263242N120 1X26W TTT 1X32W TTT*	1102 150W A21 100W A19				
REMODELER		REMODELER		REMODELER		
1103RF18N120 1103RF18N347 1X18W QT/TTT 1103RF263242N120 1103RF263242N347 1X26W TTT 1X32*/42W TTT		1103RS-CDN 150W A21 100W A19				

*See photometry p. 550 to 552.