

line voltage

Premium Die-Cast Step Baffle ☆☆☆



Versatile, low brightness downlight. Precision-fitted die-cast aluminum step baffle is finished in black or white and the recessed lamp reduces glare. Anobrite® aluminum reflector concentrates output from A and compact fluorescent lamps. Adjustable socket holder provides lamping flexibility.

Note: For dimming options, please consult the corresponding product Spec Sheet on www.canlyte.com.

<p>2005 Black Baffle 2005WH White Baffle</p>	COMPACT FLUORESCENT		INCANDESCENT		
	NON-IC	IC/AIRSEAL®	NON-IC	IC	IC/AIRSEAL®
			2002 50W PAR20*/R20 75W PAR16 60W A19 REMODELER 2003RS-CDN 50W PAR20*/R20 75W PAR16 60W A19	2002IC 50W PAR20* 50W R20	2004ICX-CDN 50W PAR20* 50W R20
<p>1005 Black Baffle 1005WH White Baffle</p>	COMPACT FLUORESCENT		INCANDESCENT		
	NON-IC	IC/AIRSEAL®	NON-IC	IC	IC/AIRSEAL®
	1001F13N120 1001F13N347 1X13W QT/TTT 1001F18N120 1001F18N347 1X18W TTT	1004ICF13N120 1004ICXF13N120 1X13W QT/TTT 1004ICF18N120 1004ICXF18N120 1X18W TTT 1004ICF26N120 1004ICXF26N120 1X26W TTT	1002 75W PAR30* 85W BR30 100W A19 1004IC-CDN 75W PAR30 54W BR30 40W A19	1002IC 75W PAR30* 75W BR30 40W A19	1004IC-CDN 50W PAR30 65W BR30 1004ICX-CDN 75W PAR30* 65W BR30 40W A19
	REMODELER	REMODELER	REMODELER		REMODELER
1003RF18N120 1003RF18N347 1X18W TTT	1004ICRF13N120 1X13W QT/TTT 1004ICRF18N120 1X18W TTT 1004ICRF26N120 1X26W TTT	1003RS-CDN 75W PAR30* 85W BR30 100W A19 1004ICRS-CDN 75W PAR30* 75W BR30 40W A19		1004ICRS-CDN 50W PAR30 65W BR30	
METAL HALIDE					
NON-IC					
1001H20HY1 1001H20HY1-347 20W PAR30		1001H39HY1 1001H39HY1-347 39W PAR30		1001H70HY1 1001H70HY1-347 70W PAR30	
<p>1105 Black Baffle 1105WH White Baffle</p>	COMPACT FLUORESCENT		INCANDESCENT		
	NON-IC	IC/AIRSEAL®	NON-IC	IC	IC/AIRSEAL®
	1101F13N120 1101F13N347 1X13W QT/TTT 1101F18N120 1101F18N347 1X18W QT/TTT 1101F263242N120 1101F263242N347 1X26/32W TTT*	1104ICF13N120 1X13W QT/TTT 1104ICF18N120 1104ICXF18N120 1X18W QT/TTT 1104ICF26N120 1104ICXF263242N120 1X26W TTT	1102 150W PAR38* 150W BR40 150W A21 1104IC-CDN 90W PAR38 120W BR40 75W A19	1102IC 90W PAR38 100W BR40 60W A19	1104IC-CDN 75W PAR38 65W BR40 40W A19 1104ICX-CDN 90W PAR38 100W BR40 60W A19
	REMODELER	REMODELER	REMODELER		REMODELER
1103RF18N120 1103RF18N347 1X18W QT/TTT 1103RF263242N120 1103RF263242N347 1X26/32W TTT*	1104ICRF13N120 1X13W QT/TTT 1104ICRF18N120 1X18W QT/TTT 1104ICRF26N120 1X26W TTT	1103RS-CDN 150W PAR38* 150W BR40 150W A21 1104ICRS-CDN 90W PAR38 120W BR40 75W A19		1104ICRS-CDN 75W PAR38 65W BR40 40W A19	
METAL HALIDE					
NON-IC					
1101H70HY1 1101H70HY1-347 70W PAR38*			1101H10HY1 1101H10HY1-347 100W PAR38		

*See photometry p. 550 to 552.