

Specular Alzak® Cone ☆☆

Versatile, low brightness downlights. Specular Alzak® heavy gauge aperture cone and recessed lamp control glare. Cone can easily be removed to facilitate maintenance.



Note: For dimming options, please consult the corresponding product Spec Sheet on www.canlyte.com.

COMPACT FLUORESCENT		INCANDESCENT				2005CL Specular Clear Alzak® 2005BA Specular Black Alzak® 2005CCD Comfort Clear™ Diffuse
NON-IC	IC/AIRSEAL®	NON-IC	IC	IC/AIRSEAL®		
		2002 50W PAR20/R20 75W PAR16 60W A19	2002IC 50W PAR20 50W R20	2004ICX-CDN 50W PAR20 50W R20		
		REMODELER				
		2003RS-CDN 50W PAR20/R20 75W PAR16 60W A19				
COMPACT FLUORESCENT		INCANDESCENT				1005CL Specular Clear Alzak® 1005BA Specular Black Alzak® 1005CCD Comfort Clear™ Diffuse
NON-IC	IC/AIRSEAL®	NON-IC	IC	IC/AIRSEAL®		
1001F13N120 1001F13N347 1X13W QT/TTT 1001F18N120 1001F18N347 1X18W TTT	1004ICF13N120 1004ICXF13N120 1X13W QT/TTT 1004ICF18N120 1004ICXF18N120 1X18W TTT 1004ICF26N120 1004ICXF26N120 1X26W TTT	1002 75W PAR30* 85W BR30 100W A19 1004IC-CDN 75W PAR30* 85W BR30 60W A19	1002IC 75W PAR30* 75W BR30 40W A19	1004IC-CDN 50W PAR30 65W BR30 40W A19 1004ICX-CDN 75W PAR30* 85W BR30 60W A19		
REMODELER	REMODELER	REMODELER		REMODELER		
1003RF18N120 1003RF18N347 1X18W TTT	1004ICRF13N120 1X13W QT/TTT 1004ICRF18N120 1X18W TTT 1004ICRF26N120 1X26W TTT	1003RS-CDN 75W PAR30 85W BR30 100W A19 1004ICRS-CDN 75W PAR30* 85W BR30 60W A19		1004ICRS-CDN 50W PAR30 65W BR30 40W A19		
METAL HALIDE						
NON-IC						
1001H20HY1 1001H20HY1-347 20W PAR30		1001H39HY1 1001H39HY1-347 39W PAR30		1001H70HY1 1001H70HY1-347 70W PAR30		
COMPACT FLUORESCENT		INCANDESCENT				1105CL Specular Clear Alzak® 1105BA Specular Black Alzak® 1105CCD Comfort Clear™ Diffuse
NON-IC	IC/AIRSEAL®	NON-IC	IC	IC/AIRSEAL®		
1101F13N120 1101F13N347 1X13W QT/TTT 1101F18N120 1101F18N347 1X18W QT/TTT 1101F263242N120 1101F263242N347 1X26/32W TTT	1104ICF13N120 1X13W QT/TTT 1104ICF18N120 1104ICXF18N120 1X18W QT/TTT 1104ICF26N120 1104ICXF263242N120 1X26W TTT	1102 150W PAR38 150W BR40 150W A21 1104IC-CDN 100W PAR38 150W BR40 75W A19	1102IC 90W PAR38* 100W BR40 60W A19	1104IC-CDN 75W PAR38 65W BR40 40W A19 1104ICX-CDN 90W PAR38* 100W BR40 60W A19		
REMODELER	REMODELER	REMODELER		REMODELER		
1103RF18N120 1103RF18N347 1X18W QT/TTT 1103RF263242N120 1103RF263242N347 1X26/32W TTT	1104ICRF13N120 1X13W QT/TTT 1104ICRF18N120 1X18W QT/TTT 1104ICRF26N120 1X26W TTT	1103RS-CDN 150W PAR38 150W BR40 150W A21 1104ICRS-CDN 100W PAR38 150W BR40 75W A19		1104ICRS-CDN 75W PAR38 65W BR40 40W A19		
METAL HALIDE						
NON-IC						
1101H70HY1 1101H70HY1-347 70W PAR38*			1101H10HY1 1101H10HY1-347 100W PAR38			

*See photometry p. 550 to 552.