



Ceiling Opening: 3-3/4" (95mm)

**Complete fixture consists of the Trim and Frame-in Kit. Select each separately.**

Reflector Trim		Frame-in Kit		Lamp
<b>348STX</b>	Brushed steel	Remodeler	<b>3401MREX</b>	37W MR16 IR
<b>348WHX</b>	White paint	Non-IC	<b>302MREX</b>	50W MR16 / 37W MR16 IR
		IC / AirSeal®	<b>302MRAICEX</b>	37W MR16 IR

### Features

- Housing:** 25 ga steel. Black painted finish.
- Residence Mounting Clips:** Factory-installed; zinc plated spring steel; free-hand installation.
- Flange:** Die-cast aluminum 0.060" (1.5mm) thick.
- Adjustable Lampholder Assembly Support:** Die-cast aluminum, rotates 358° horizontally and 0° to 35° vertically. Black painted finish.
- Mounting Clips (2):** 24 ga. stainless steel. Provides easy snap-in / snap-out action.
- Lamp guard:** 2" (51mm) dia. borosilicate glass.

**Note:** For complete Frame-in Kit specifications, refer to the 300X series Frame-in Kit specification sheets.

### Accessories

- 2" (51mm) dia. Specialized Filters and Louvers.
- AF2SY** Symmetric: Prismatic Spread Lens (55°).
  - AF2AS** Asymmetric: Beam Elongator (5° x 55°).
  - AF2FR** Light Frost: Softens light beam.
  - AF2PF** Perimeter Frost.
  - AF2UV** UV Filters: Blocks UV radiation.
  - AF2IR** Infrared Filter: Block infrareds.
  - 300XTC** Thick ceiling housing kit.

### Labels

CSA, UL Suitable for damp locations.

Job Information	Type:
<b>Job Name:</b>	
<b>Cat. No.:</b>	
<b>Lamp(s):</b>	
<b>Notes:</b>	