



Complete fixture consists of the Trim and Frame-in Kit. Select each separately.

Reflector Trim		Frame-in Kit		Lamp
<b>344ASTX</b>	Brushed steel	Remodeler	<b>3401MREX</b>	37W MR16 IR
<b>344AWHX</b>	White paint	Non-IC	<b>302MREX</b>	50W MR16 / 37W MR16 IR
		IC / AirSeal®	<b>302MRAICEX</b>	37W MR16 IR

## Features

- Housing:** 25 ga steel. Black painted finish.
- Residence Mounting Clips:** Factory-installed; zinc plated spring steel; free-hand installation.
- Flange:** Die-cast aluminum 0.060" (1.5mm) thick.
- Lampholder Assembly Support:** Die-cast aluminum, rotates 358° horizontally and 0° to 35° vertically. Can be locked in vertical position.
- Mounting Clips (2):** 24ga. stainless steel. Provides easy snap-in / snap-out action.
- Lamp guard:** 2" (51mm) dia. borosilicate glass.
- Truncate Baffle:** Die-cast aluminum with stepped conical surface for low brightness. Black painted finish.

**Note:** For complete Frame-in Kit specifications, refer to the 300X series Frame-in Kit specification sheets.

## Accessories

- 2" (51mm) dia. Specialized Filters and Louvers.
- AF2SY** Symmetric: Prismatic Spread Lens (55°).
  - AF2AS** Asymmetric: Beam Elongator (5° x 55°).
  - AF2LF** Light Frost: Softens light beam.
  - AF2PF** Perimeter Frost.
  - AF2UV** UV Filters: Blocks UV radiation.
  - AF2IR** Infrared Filter: Block infrareds.
  - 300XTC** Thick ceiling housing kit.

## Labels

**CSA, UL** Suitable for damp locations.

## Job Information

## Type:

**Job Name:**

**Cat. No.:**

**Lamp(s):**

**Notes:**