

**Basic Grooved Baffle** ☆

Aluminum reflector grooved on the inside for baffle appearance. Interior painted black to reduce glare. Operates effectively with PAR and BR lamps. A lamps recommended for white version only. White version is all white for a uniform look.



COMPACT FLUORESCENT		INCANDESCENT				<b>R520-12BK</b> Black Grooves <b>R520-12WH</b> White Grooves (Carton of 12)
NON-IC	IC/AIRSEAL®	NON-IC	IC	IC/AIRSEAL®		
		<b>2002</b> 50W PAR20 50W R20	<b>2002IC</b> 50W PAR20 50W R20	<b>2004ICX-CDN</b> 50W PAR20 50W R20		<b>R620-12BK</b> Black Grooves <b>R620-12WH</b> White Grooves (Carton of 12)
		<b>1002</b> 75W PAR30 85W BR30 75W A19 <b>1004IC-CDN</b> 75W PAR30 85W BR30	<b>1002IC</b> 75W PAR30 75W BR30 40W A19	<b>1004IC-CDN</b> 50W PAR30 45W BR30 <b>1004ICX-CDN</b> 75W PAR30 85W BR30		
		<b>REMODELER</b>		<b>REMODELER</b>		
		<b>1004ICRS-CDN</b> 75W PAR30 85W BR30		<b>1004ICRS-CDN</b> 50W PAR30 45W BR30		
COMPACT FLUORESCENT		INCANDESCENT				<b>R720-12BK</b> Black Grooves <b>R720-12WH</b> White Grooves (Carton of 12)
NON-IC	IC/AIRSEAL®	NON-IC	IC	IC/AIRSEAL®		
		<b>1102</b> 150W PAR38 150W BR40 100W A19 <b>1104IC-CDN</b> 150W PAR38 120W BR40	<b>1102IC</b> 90W PAR38 100W BR40 60W A19	<b>1104IC-CDN</b> 75W PAR38 85W BR40 52W A19 <b>1104ICX-CDN</b> 90W PAR38 100W BR40		
		<b>REMODELER</b>		<b>REMODELER</b>		
		<b>1104ICRS-CDN</b> 150W PAR38 120W BR40		<b>1104ICRS-CDN</b> 75W PAR38 85W BR40 52W A19		