

# INCANDESCENT LAMPS

Watts	Bulb	Base	Product Number	Symbols, Footnotes	Ordering Code	Volts	Pkg. Qty.:	Description	Class Filament	LCL (In.)	MOL (In.)	Rated Avg. Life (Hrs.)(93)	Approx. MBCP*	Lumens
250	BR40	Med.	38932-0	▲ (27, 87)	250BR40/I 4/I	120	4	Clear Reflector Infrared	C, C-9		6½	5000		
			20205-1	▲ (27, 87)	250BR40/I/TG 4/I	120	4	TuffGuard Coated Clr. Ref. Infrared	C, C-9		6½	5000		
			14011-1	▲ (27, 87)	250BR40/I 12/I PRO	130	12	ProPack Clear Reflector Infrared	C, C-9		6½	5000		1600
	PAR38	Med. Skt.	37432-2	□ (53, 82)	K250PAR38/FL	120-130	12	PAR Floodlight (Krypton)	C, CC-6		5%	4000	5000	3100
			37433-0	□ (53, 82)	K250PAR38/SP	120-130	12	PAR Spotlight (Krypton)	C, CC-6		5%	4000		3100
	R40	Med.	38933-8	▲\$ (27,87,89)	250R40/HR 4/I	120	4	Red Bowl Heat Ray	C, C-9		6%	5000		
15932-7			▲\$ (27,87,89)	250R40/HR/TG 4/I	120	4	TuffGuard Ctd. Red Bowl Heat Ray	C, C-9		6%	5000			
300	BR40	Med.	14343-8	▲\$ (87)	300BR/FL	120-130	24	Reflector Flood	C, CC-11		6½	2000		2480
			PAR56	Mog. End Prong	23382-5		300PAR56/MFL	120	8	PAR Med. Flood	C, CC-13		5	2000
	23405-4	(9, 55)			300PAR56/MFL	130	8	PAR Med. Flood	C, CC-13		5	2000		
	23388-2	(9, 55)			300PAR56/WFL	120	8	PAR Wide Flood	C, CC-13		5	2000		
	23410-4	(9, 55)			300PAR56/WFL	130	8	PAR Wide Flood	C, CC-13		5	2000		
	23378-3	(9, 46, 55)			300PAR56/NSP	120	8	PAR Narrow Spotlight	C, CC-13		5	2000		
	PS25	Med.	28177-4	▲	300M/IF	120-130	60	Frost	C, CC-8		6½%	750		6230
								Ratings @120V=282W				1280		5471
			38941-1	▲	300M/IF	120	6	Frost	C, CC-8		6½%	750		6300
			20206-9	▲	300M/99IF/TG	120/130	60	TuffGuard Frost Coated Lamp	C, CC-8		6½%	2500		5060
			13391-8	▲	300M	120-130	12	Clear	C, CC-8	5¼	6½%	750		6280
								Ratings @120V=265W				2120		4625
			35008-2	▲	300M/99IF	120	60	Frost Extended Service	C, CC-8		6½%	2500		4044
			35009-0	▲	300M/99IF	130	60	Frost Extended Service	C, CC-8		6½%	2500		506
								Ratings @120V=265W				7130		4044
			35007-4	▲	300M/99	130	60	Clear Extended Service	C, CC-8	5¼	6½%	2500		5300
						Ratings @120V=265W				7134		4044		
	PS30	Med.	14307-3	▲	300M/PS30IF	120-130	60	Frost	C, C-9		8½%	750		5000
								Ratings @120V=265W				2120		3800
			14306-5	▲	300M/PS30	120-130	60	Clear	C, C-9		8½%	750		5000
							Ratings @120V=265W				2120		3800	
20207-7	▲	300M/PS30/IF/TG	120-130	60	TuffGuard Coated Lamp Frost	C, C-9		8½%	750		5000			
					Ratings @120V=265W				2120		3800			
14294-3		300M/PS30/35	120-130	60	Frost Industrial Service	C, C-9		8½%	3500		3800			
					Ratings @120V=265W				9900		2885			

For the most current product information, go to the e-catalog on [www.philips.com](http://www.philips.com)  
Incandescent symbols and footnotes located on page 149



BR40  
Med.



PAR38  
Med. Skt.



R40  
Med.



PAR56  
Mog. End Prong



PS25  
Med.



PS30  
Med.