



Energy Saving Elegance.

EnduraLED Candle

The Philips EnduraLED™ Candles offer decorative energy saving ambience with the elegant effect of incandescent candles. Available in bent and blunt tip shapes, their unique design provides light in all directions, giving lighting designers a long life alternative to incandescent sources. Energy saving, long life decorative LED candles lower cost with reduced wattage and re-lamp frequency.

Benefits

- Philips is the global leader in light and a leader in LED technology.
- Philips knows LED light and stands behind the EnduraLED products with a warranty.
- Philips' commitment to innovation and quality provides the confidence of partnering with an industry leader.

Features

- Instant-on light.
- Emits virtually no UV/IR light in the beam.
- Similar ambience as traditional incandescent candles.
- 3000K color temperature.
- Designed to last 15,000 hours rated average life (1,2)
- 3-year Warranty period.
- Contains no mercury
- Rated average life is the length of operation (in hours) at which point an average of 50% of the lamps will still be operational and 50% will not.
- Rated average life based on engineering testing and probability analysis.
- Available in 3 Watt Clear and Frost, Blunt and Bent tip.



Application

- Ideal for wall sconces and decorative lighting.

Related products



Dimensional drawing



E12 B10.5

Product	C (Norm)	D (Norm)
LED E12 3000K 120V B10.5 Frosted	-	-
LED E12 3000K 120V B10.5 Clear	-	-
LED 2W WW 2700K 120V B10.5 Clear	-	-

E12 BA9

Product	C (Norm)	D (Norm)
LED E12 3000K 120V BA9 Clear	-	-
LED E12 3000K 120V BA9 Frosted	-	-
LED 2W WW 2700K 120V BA9 Clear	-	-

Compare table

Product number	Full product name	Wattage	Color Code	Cap-Base	Bulb	Bulb Finish	Voltage	Luminous Flux	Color rendering index	Color Temperature	Dimmable
406058	EnduraLED 2.5W 3000K 120V BA9 CL	2.5	-	E12	BA9	Clear	120	30	80	3000	No
406074	EnduraLED 2.5W 3000K 120V B10.5 CL	2.5	WH	E12	B10.5	Clear	120	30	80	3000	No
407964	EnduraLED 2W 2700K 120V BA9 CL	2	WW	-	BA9	Clear	120	70	90	2700	-
407972	EnduraLED 2W 2700K 120V B10.5 CL	2	WW	-	B10.5	Clear	120	70	90	2700	-

Product number	Full product name	Wattage	Color Code	Cap-Base	Bulb	Bulb Finish	Voltage	Luminous Flux	Color rendering index	Color Temperature	Dimmable
410209	EnduraLED 3W 2700K BA11 Dimmable	3	WW	E12	BA11	Clear	120	70	90	2700	Yes
410217	EnduraLED 3W 2700K B11 Dimmable	3	WW	E12	B11	Clear	120	130	90	2700	Yes
406066	EnduraLED 2.5W 3000K 120V BA9 Frosted	2.5	WH	E12	BA9	Frosted	120	30	80	3000	No
406082	EnduraLED 2.5W 3000K 120V B10.5 Frosted	2.5	WH	E12	B10.5	Frosted	120	30	80	3000	No

Compare table

Product number	Full product name	Rated Luminous Flux	Rated Life-time (hours)
406058	EnduraLED 2.5W 3000K 120V BA9 CL	-	15000
406074	EnduraLED 2.5W 3000K 120V B10.5 CL	-	15000
407964	EnduraLED 2W 2700K 120V BA9 CL	70	20000
407972	EnduraLED 2W 2700K 120V B10.5 CL	70	20000
410209	EnduraLED 3W 2700K BA11 Dimmable	70	20000
410217	EnduraLED 3W 2700K B11 Dimmable	130	20000
406066	EnduraLED 2.5W 3000K 120V BA9 Frosted	-	15000
406082	EnduraLED 2.5W 3000K 120V B10.5 Frosted	-	15000



© 2011 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2011, February 24
data subject to change