



Halogená® BR30 Indoor Flood

Halogená Indoor Flood 60W ES BR-30 43D REFL 1CT

Meet the Halogená® collection of light bulbs, the elegant, long life alternative to ordinary household light. Halogená provides bright, white light that lasts two years*. Their long life makes them great for hard-to-reach fixtures. Fewer replacements means less hassle. But that's not all, Halogená light bulbs are also fully dimmable, which can save energy. From Decorative to PARs, from the Classic to easy grip Reflectors, Halogená light bulbs provide bright, white light, indoors or out.

Product data

• General Characteristics

| | |
|------------------------------|--------------------------------------|
| Base | Medium [Single Contact Medium Screw] |
| Base Information | Brass [Brass Base] |
| Bulb | BR30 |
| Bulb Material | Soft Glass |
| Bulb Finish | Reflector |
| Operating Position | Universal [Any or Universal (U)] |
| Main Application | General Lighting |
| Rated Avg. Life @ 120v | 3000 hr |
| Estimated Energy Cost/YR | 7.23 \$ |
| Life with 3h/day use [years] | 2.7 an |

• Electrical Characteristics

| | |
|-------------|-------|
| Energy Used | 60 W |
| Voltage | 120 V |

• Light Technical Characteristics

| | |
|-----------------------|-------------------------|
| Beam Description | Flood [Flood] |
| Beam Angle | 43 D |
| Approx. MBCP | 500 (nom), 650 (max) cd |
| Color Rendering Index | 100 Ra8 |

| | |
|------------------------|-----------|
| Color Temperature | 2790 K |
| Lumens (Brightness) | 675 Lm |
| Initial Lumens | 700 Lm |
| Luminous Efficacy Lamp | 11.7 Lm/W |

• Product Dimensions

| | |
|-------------------------------|----------------|
| Max. Overall Length (MOL) - C | 5.374 (max) in |
| Diameter D | 3.75 in |

• Product Data

| | |
|-----------------------------|---|
| Order code | 928601106514 |
| Full product code | 928601106514 |
| Full product name | Halogená Indoor Flood 60W ES BR-30 43D REFL 1CT |
| Order product name | 60W ES BR-30 43D REFL 1CT |
| Pieces per pack | 1 |
| Packs per outerbox | 6 |
| Bar code on pack - EAN1 | 067805300506 |
| Bar code on outerbox - EAN3 | 50067805300501 |
| Logistic code(s) - 12NC | 928601106514 |

PHILIPS

sense and simplicity