

HALOGEN LAMPS

Long Life IR, PAR36, PAR38 Lamps

Watts	Bulb	Base	Product Number	Symbols, Footnotes	Ordering Code	Volts	Pkg. Qty.‡	Description	Class, Filament	MOL (In.)	Rated Avg. Life (Hrs.)(93)	Approx. MBCP*	Lumens
-------	------	------	----------------	--------------------	---------------	-------	------------	-------------	-----------------	-----------	----------------------------	---------------	--------

HALOGEN LONG LIFE IR PAR30S SHORT LAMPS FEATURING HALOGEN INFRARED TECHNOLOGY AND WISO REFLECTOR (82, 86)

These lamps are 130V lamps run on 120V.

45	PAR30S	Med.	13850-3	\$Ⓜ	45PAR30S/IRC/HAL/SP10	120	15	Spot 10°	C, CC-8	3%	6000	10,000	650
			13851-1	\$Ⓜ	45PAR30S/IRC/HAL/FL25	120	15	Flood 25°	C, CC-8	3%	6000	2340	650
			13852-9	\$Ⓜ	45PAR30S/IRC/HAL/WFL40	120	15	Wide Flood 40°	C, CC-8	3%	6000	1050	650

HALOGEN PAR36 LAMPS

11	PAR36	MP	15683-6		11 PAR36Q/FL30	12	6	PAR, Flood	C, C-6	2%	2000	—	60
36	PAR36	MP	15685-1		36OAR36Q/FL30	12	6	PAR, Flood	C, C-6	2%	4000	—	450
50	PAR36	MP	15684-4		50PAR36Q/FL30	12	6	PAR, Flood	C, C-6	2%	4000	—	650
			13082-3		50PAR36Q/VNSP6	12	12	PAR, Narrow Spot	C, C-6	2%	4000	35,000	400

HALOGEN PAR38 LAMPS (82, 86)

45	PAR38	Med.Skt.	22946-8	Ⓜ	45PAR38/HAL/SP10	120	12	Spot 10°	C, CC-8	5%	3000	5800	530
			20231-7	Ⓜ	45PAR38/HAL/FL25	120	12	Flood 25°	C, CC-8	5%	3000	2000	530
60	PAR38	Med.Skt.	14482-4	Ⓜ	60PAR38/HAL/SP10	120	12	Spot 10°	C, CC-8	5%	3000	10,500	800
			14483-2	Ⓜ	60PAR38/HAL/FL25	120	12	Flood 25°	C, CC-8	5%	3000	3200	800
			14484-0	Ⓜ	60PAR38/HAL/WFL40	120	12	W. Flood 40°	C, CC-8	5%	3000	1300	800
75	PAR38	Med.Skt.	14485-7	Ⓜ	75PAR38/HAL/SP10	120	12	Spot 10°	C, CC-8	5%	3000	13,000	1050
			14486-5	Ⓜ	75PAR38/HAL/FL25	120	12	Flood 25°	C, CC-8	5%	3000	3800	1050
90	PAR38	Med.Skt.	23069-8	Ⓜ	90PAR38/HAL/SP10	120	12	Spot 10°	C, CC-8	5%	3000	14,500	1350
			20234-1	Ⓜ	90PAR38/HAL/FL25	120	12	Flood 25°	C, CC-8	5%	3000	4500	1350
			27429-0	Ⓜ	90PAR38/HAL/FL	120	15	Flood 28°	C, CC-8	5%	2000	4500	1370
			38925-4	Ⓜ	90PAR38/HAL/FL	120	18	Flood 28°	C, CC-8	5%	2000	4500	1370
			14487-3	Ⓜ	90PAR38/HAL/WFL40	120	12	Wide Flood 40°	C, CC-8	5%	3000	2200	1350

HALOGEN PAR38 LAMPS 130V (82, 86)

45	PAR38	Med.Skt.	22947-6	\$Ⓜ	45PAR38/HAL/SP10	130	12	Spot 10°	C, CC-8	5%	2500	5800	530		
									Ratings @ 120V=40W			5000	4960	410	
	Standard Reflector		22949-2	\$Ⓜ	45PAR38/HAL/FL25	130	12	Flood 25°	C, CC-8	5%	2500	2000	530		
									Ratings @ 120V=40W			5000	1600	410	
60	PAR38	Med.Skt.	14488-1	\$Ⓜ	60PAR38/HAL/SP10	130	12	Spot 10°	C, CC-8	5%	3000	10,500	800		
									Ratings @ 120V=53W			6000	8400	610	
			14490-7	\$Ⓜ	60PAR38/HAL/FL25	130	12	Flood 25°	C, CC-8	5%	3000	3200	800		
										Ratings @ 120V=53W			6000	2560	610
			14489-9	\$Ⓜ	60PAR38/HAL/FL25	130	12	Flood 25°	C, CC-8	5%	3000	3200	800		
							Ratings @ 120V=53W			6000	2560	610			
			14491-5	\$Ⓜ	60PAR38/HAL/WFL40	130	12	W. Flood 40°	C, CC-8	5%	3000	1300	800		
								Ratings @ 120V=53W			6000	1040	610		

For the most current product information, go to the e-catalog on www.philips.com
Halogen symbols and footnotes located on page 70

