



Philips Halogen
Mini-Reflector - Flood

20W
GU5.3 base
Clear
Dimmable

046677162474

Brilliant alternative to incandescents

Enhance your home with bright, white light

Philips 20W dimmable indoor halogen mini reflector flood provides bright sparkling accent light. An efficient alternative to 20W incandescents, it has no mercury and saves a lot of money

Sparkling light

- Bright alternative to incandescent

Easy to use

- Dimmable
- Instant On

PHILIPS

Specifications

Bulb characteristics

- Shape: Reflector Flood
- Type: MRC16, MR16
- Base: GU5.3
- Voltage: 12 V
- Dimmable

Power consumption

- Wattage: 20 W

Light characteristics

- Application: Accent light
- Color rendering index (CRI): 100
- Color temperature: 3000 K
- Light output: 430 lumen
- Light effect/finish: Clear

Durability

- Average life (at 2.7 hrs/day): 2 year(s)
- Lifetime of lamps: 2000 hour(s)

Highlights

Alternative to incandescent

This halogen light bulb provides a bright, sparkling light, ideal for adding brilliance and drama to your home.

Dimmable

This bulb can be used with most dimmers to create your desired ambience.

Instant On

Just by turning the switch, your room is at full brightness. No slow starting or waiting.



Issue date 2016-10-21

Version: 1.0.3

12 NC: 9240 495 17117

© 2016 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com

*Based on 3 hrs/day, 11g/kWh. Cost depends on rates and use.

* 2.7 years means rated average life based on engineering testing and probability analysis where the bulb is used on average 3 hours/day, 7 days a week.